

# Specifications




Photo is representative

## Eaton TP683

Eaton Crouse-Hinds series Masonry Box, (4) 1/2", (4) 3/4", 2-1/2", (2) 1/2", (2) 3/4", Steel, Two-gang, (2) 1/2", (2) 3/4", 31.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series masonry box
<b>CATALOG NUMBER</b>	TP683
<b>UPC</b>	786189106831
<b>PRODUCT LENGTH/DEPTH</b>	3.75 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	1.03 lb



### Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous

### Product specifications

**DEPTH** 2-1/2"

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC

<b>NUMBER OF GANGS</b>	Two-gang
<b>END KNOCKOUTS</b>	(2) 1/2 in, (2) 3/4 in
<b>SIDE KNOCKOUTS</b>	(2) 1/2 in, (2) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(4) 1/2 in, (4) 3/4 in
<b>CAPACITY</b>	31 cubic in
<b>MATERIAL</b>	Steel

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Masonry Boxes catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Masonry Boxes Canadian certification</a> <a href="#">Steel Masonry Boxes UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP683</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications




Photo is representative

## Eaton TP683

Eaton Crouse-Hinds series Masonry Box, (4) 1/2", (4) 3/4", 2-1/2", (2) 1/2", (2) 3/4", Steel, Two-gang, (2) 1/2", (2) 3/4", 31.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series masonry box
<b>CATALOG NUMBER</b>	TP683
<b>UPC</b>	786189106831
<b>PRODUCT LENGTH/DEPTH</b>	3.75 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	1.03 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous
----------------------------	------------------------

### Product specifications

<b>DEPTH</b>	2-1/2"
--------------	--------

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC

<b>NUMBER OF GANGS</b>	Two-gang
<b>END KNOCKOUTS</b>	(2) 1/2 in, (2) 3/4 in
<b>SIDE KNOCKOUTS</b>	(2) 1/2 in, (2) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(4) 1/2 in, (4) 3/4 in
<b>CAPACITY</b>	31 cubic in
<b>MATERIAL</b>	Steel

## Resources

### CATALOGS

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

### CERTIFICATION REPORTS

[Steel Masonry Boxes Canadian certification](#)

[Steel Masonry Boxes UL certification](#)

### SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP683](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

