



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR1712R 250V 17 1/2A 2X9/16 RK5 TD Fuse *Mersen Fuses*

| | |
|------------------|--|
| Catalog Number | TR1712R |
| Manufacturer | Mersen Fuses |
| Description | Fuse TR-R - Class RK5 - Time-Delay 250VAC 160VDC 17.5A Ferrule Tri-Onic® |
| Weight per unit | 0.0500 (lbs/each) |
| Product Category | Current Limiting |

Features

| | |
|-------------------|-----------|
| AC Voltage Rating | 250 |
| amperage rating | 17.5 |
| class | Class RK5 |
| connection | Ferrule |
| interrupt rating | 200 |
| Voltage Rating | 250 |

Material, Color, and Finish

| | |
|---------------|----------|
| Body Material | PolyTube |
|---------------|----------|

Dimensions and Weight

| | |
|------|----------|
| Size | 2 x 0.56 |
|------|----------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 250V 17 1/2A 2X9/16 RK5 TD FUSE |
| extra long description | Mersen TR17-1/2R Fuse TR-R - Class |
| Features | Tri-Onic TR-R current-limiting time-delay fuses are engineered for overcurrent protection of motors, transformers, service entrance equipment, feeders and branch-circuits. The time-delay characteristics of the TR-R safely handle harmless starting currents and inrush currents associated with today's motors and transformers. |
| Long Description | Fuse TR-R - Class RK5 - Time-Delay 250VAC 160VDC 17.5A Ferrule Tri-Onic® |
| Product Type | Fuse TR-R - Class RK5 - Time-Delay 250VAC 160VDC 17.5A Ferru |
| Short Description | 250V 17 1/2A 2x9/16 RK5 T |
| Special Features | Time-delay Current-limiting AC & DC rated Optional solid state SmartSpot blown fuse indicator Time-delay for motor start-ups and transformer inrush currents without nuisance opening Current-limiting for low peak let-thru current Rejection-style design prevents replacement errors (when used with recommended fuse blocks) Easy-to-read label for quick brand recognition and replacement Metal-embossed date and catalog number for traceability and lasting identification Fiberglass body provides dimensional stabili |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Mersen |
| GTIN | 00782001747831 |
| Manufacturers Part Number | TR17-1/2R |
| UPC | 782001747831 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type | CLASS RK5 |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.05 |

Uses, Certifications, and Standards

| | |
|-------------------|--|
| Application | Motor circuits Mains Feeders Branch circuits Transformers Service entrance equipment General-purpose equipment |
| Mounting standard | Clip UL listed to standard 248-12 File E2137 CSA certified to standard C22.2 no. 248.12 DC listed to UL standard 248 TRS only |