

# Eaton TRL04

Catalog Number: TRL04

Eaton 4-function Universal TR Series Timing Relay, style terminals, 0.05 seconds-100 hours time delay, 24-240 Vac/dc input voltage, Compact DIN rail mount, SPDT contact configuration, IP40 enclosure



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton TR timing relay	TRL04
<b>UPC</b>	<b>Product Length/Depth</b>
786685313573	1.3 in
<b>Product Height</b>	<b>Product Width</b>
3.43 in	1.8 in
<b>Product Weight</b>	<b>Warranty</b>
0.09 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Compliances</b>	<b>Certifications</b>
CE Marked TUV	CSA Certified cULus Listed

defaultTaxonomyAttributeLabel

Frequency rating

50-60 Hz

Enclosure

IP40

Enclosure material

Self-extinguishing plastic

Contact configuration

SPDT

Time delay

0.05 seconds-100 hours

Series

TR

Functions

ON/OFF delay

Power triggered

Single shot leading edge voltage controlled

Flasher-pause first

Input voltage

24-240 Vac/dc

Mounting method

Compact DIN rail

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Installation instructions

TRL04 and TRL07 Installation Instructions

Specifications and datasheets

Eaton Specification Sheet - TRL04



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia

# Eaton TRL04

Catalog Number: TRL04

Eaton 4-function Universal TR Series Timing Relay, style terminals, 0.05 seconds-100 hours time delay, 24-240 Vac/dc input voltage, Compact DIN rail mount, SPDT contact configuration, IP40 enclosure



## General specifications

Product Name	Catalog Number
Eaton TR timing relay	TRL04
UPC	Product Length/Depth
786685313573	1.3 in
Product Height	Product Width
3.43 in	1.8 in
Product Weight	Warranty
0.09 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked TUV	CSA Certified cULus Listed

defaultTaxonomyAttributeLabel

Frequency rating

50-60 Hz

Enclosure

IP40

Enclosure material

Self-extinguishing plastic

Contact configuration

SPDT

Time delay

0.05 seconds-100 hours

Series

TR

Functions

ON/OFF delay

Power triggered

Single shot leading edge voltage controlled

Flasher-pause first

Input voltage

24-240 Vac/dc

Mounting method

Compact DIN rail

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Installation instructions

TRL04 and TRL07 Installation Instructions

Specifications and datasheets

Eaton Specification Sheet - TRL04



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia