



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TSDCL303PTC Toggle Slide Dimmer CFL/Led/Incsp/3W 300W Tri-Colo *Pass & Seymour/Legrand*

Catalog Number	TSDCL303PTC
Manufacturer	Pass & Seymour/Legrand
Description	Trademaster® Toggle Slide Dimmer Is Designed For Use With Compact Fluorescent or Led Lighting Fixtures. This Single Pole 3-Way Switch Can Be Used In A Two-Location Layout. The Slide Can Be Set to Your Preferred Level and Then Toggle On and Off Providing Instant Repeatability. This Switch Offers Dependability and A Lifetime Warranty.
Weight per unit	0.2500 (lbs/each)
Product Category	Lighting Dimmers

### Features

Number of Switches	1.0
Poles	1
Switch Type	Slider, Rocker
Wattage	700
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Descriptions

Description	TOGGLE SLIDE DIMMER CFL/LED/INCSP/3W 300W TRI-COLO
extra long description	P&S TSDCL303PTC TOG SLIDE DIM CFL/L
Features	Preset
Long Description	TradeMaster® Toggle Slide Dimmer is designed for use with compact fluorescent or LED lighting fixtures. This single pole 3-way switch can be used in a two-location layout. The slide can be set to your preferred level and then toggle on and off providing instant repeatability. This switch offers dependability and a lifetime warranty.
Product Type	Tog Slide Dim CFL/Led/Incsp/3W 300W Tri

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007215977
Manufacturers Part Number	TSDCL303PTC
UPC	785007215977

### Taxonomies, Classifications, and Categories

Category Description	TOGGLE SWITCHES
----------------------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Trade Size

Amperage ..... 2.5

## Packaging

Carton ..... 1

Package ..... 24

Weight Per each ..... 0.25