




SNAP TO STUD TELESCOPING SCREW GUN BOX BRACKET

CATALOG NUMBER

TSGB1624S



CERTIFICATIONS



FEATURES

Snap to stud function makes installation fast and easy, saving time and increasing productivity

Self-leveling feature ensures the bracket is always square to the stud, for a consistent and professional installation

Pre-configured for 2-1/8" deep boxes and only a simple adjustment needed for 1-1/2" deep boxes

Can mount multiple boxes

Requires only two screws to install

PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Stud Spacing: 15 3/4" - 25"

Box Depth: 1 1/4"; 2 1/8"

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500




Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER



SNAP TO STUD TELESCOPING SCREW GUN BOX BRACKET

CATALOG NUMBER

TSGB1624S



CERTIFICATIONS



FEATURES

Snap to stud function makes installation fast and easy, saving time and increasing productivity

Self-leveling feature ensures the bracket is always square to the stud, for a consistent and professional installation

Pre-configured for 2-1/8" deep boxes and only a simple adjustment needed for 1-1/2" deep boxes

Can mount multiple boxes

Requires only two screws to install

PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Stud Spacing: 15 3/4" - 25"

Box Depth: 1 1/4"; 2 1/8"

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER