



Commercial grade receptacles


Commercial grade straight blade receptacles

Product description


2-pole, 3-wire grounding
 15A, 125V/AC
 20A, 125V/AC
 NEMA 5-15R, 5-20R



TRBR15



TR1877



WRBR15

Tamper resistant commercial grade receptacles



Rating	A	V/AC	NEMA	Description	Color suffix	Catalog no.	
15	125	5-15R	Duplex receptacle, back & side wire	A, B, BK, GY, LA, V, W	□ TRBR15__	• •	
			Single receptacle, side wire	A, B, BK, LA, V, W	□ TR817__*	• •	
			Decorator duplex receptacle, back & side wire	LA, V, W	□ TR6252__	• •	
			Decorator single receptacle, back & side wire	B, BK, V, W	□ TR6250__	• •	
			Duplex receptacle, side wire	A, B, BK, GY, LA, V, W	□ TRCR15__*		
20	125	5-20R	Duplex receptacle, back & side wire	A, B, BK, GY, LA, RD, V, W	□ TRBR20__	• •	
			Single receptacle, side wire	A, B, BK, LA, V, W	□ TR1877__*	• •	
			Decorator duplex receptacle, back & side wire	A, B, BK, GY, LA, V, W	□ TR6352__	• •	
			Decorator single receptacle, side wire	LA, V, W	□ TR6350__*	• •	
			Duplex receptacle, side wire	A, B, BK, GY, LA, V, W	□ TRCR20__*		

* Not Fed Spec

Weather resistant commercial grade receptacles



Rating	A	V/AC	NEMA	Description	Color suffix	Catalog no.	
15	125	5-15R	Duplex receptacle, back & side wire	B, V, W	□ WRBR15__	• •	
20	125	5-20R	Duplex receptacle, back & side wire	B, V, W	□ WRBR20__	• •	

Tamper & weather resistant commercial grade receptacles



Rating	A	V/AC	NEMA	Description	Color suffix	Catalog no.	
15	125	5-15R	Duplex receptacle, back & side wire	B, GY, V, W	□ TWRBR15__	• •	
20	125	5-20R	Duplex receptacle, back & side wire	B, V, W	□ TWRBR20__	• •	

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)



Specification information: Tamper resistant commercial receptacles: A-32, Weather resistant commercial receptacles: A-32, Tamper & weather resistant commercial receptacles: A-32

Compliances, specifications and availability are subject to change without notice.

➤ ArrowLink option available. Add "M" suffix to standard catalog number (example AH8300W, AH8300WM). For ordering information on ArrowLink & ArrowLink SPD connectors, see Page A-5

Build-to-spec customizable devices - Page A-6

RoHS compliant - Page Q-32

TR Tamper resistant WWR Weather resistant TWR Tamper & weather resistant