



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY25M 7.31" Ty-Rap (Bulk)

Abb Installation Products, Inc

Catalog Number	TY25M
Manufacturer	Abb Installation Products, Inc
Description	High Performance Cable Tie For Indoor Applications, Natural Color Nylon 6.6, Length Of 186MM (7.3 Inches) For Bundle Diameter Up to 48MM (1.89 Inches), Width Of 4.83MM (0.19 Inches), Tensile Strength Rating Of 222 Newtons (50 Pounds), Operating Temperature Of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), Bulk Pack
Weight per unit	0.0020 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	50;222
------------------	--------

Dimensions and Weight

Length	7.2
Thickness	0.05
Width	0.19

Descriptions

Description	7.31" TY-RAP (BULK)
extra long description	ABB TY25M CABLE TIE 50LB 7.31IN NAT
Long Description	High Performance Cable Tie for Indoor applications, Natural Color Nylon 6.6, Length of 186mm (7.3 Inches) for Bundle Diameter up to 48mm (1.89 Inches), Width of 4.83mm (0.19 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), Bulk Pack
Product Type	Cable Tie 50LB 7.31IN Natural Nylon
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210824574
Manufacturers Part Number	TY25M
UPC	786210824574

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 1000

Packaging

Carton 1000

Weight Per each 0.002

Uses, Certifications, and Standards

standard UL E49405, CSA 2884