




MILBANK
ENERGY AT WORK

U5934-XL-BLG



Catalog Number	U5934-XL-BLG
Marketing Product Description	4 Terminal Ringless Small Closing Plate 7-8 In Barrel Lock Ground With Bracket Provision
UPC	784572592278
Length (IN)	3.61
Width (IN)	8
Height (IN)	11.5
Brand Name	Milbank
Type	Ringless Meter Socket
Application	Meter Socket
Standard	UL Listed;Type 3R
Voltage Rating	600 Volts Alternating Current
Amperage Rating	100 Continuous Ampere
Phase	1 Phase
Frequency Rating	60 Hertz
Size	3.61L x 8W x 11.5H
Number Of Cutouts	0
Cutout Size	No Main Breaker
Cable Entry	Overhead or Underground
Terminal	Single Mechanical
Insulation	Glass Polyester
Mounting	Surface Mount

Enclosure	G90 Galvanized Steel with Powder Coat Finish
-----------	--

Jaw Quantity	4 Terminal
--------------	------------

Bypass Type	No Bypass
-------------	-----------

Number of Meter Positions	1 Position
---------------------------	------------

Equipment Ground	Ground Bar
------------------	------------

Hub Opening	Small Closing Plate
-------------	---------------------





Line Side Wire Range	12 - 1/0 AWG
----------------------	--------------

Load Side Wire Range	12 - 1/0 AWG
----------------------	--------------

Number Of Receptacles	0
-----------------------	---

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	6	U/L MNTG.EMBOSS
B	1	¼ SOLID K.O.
C	3	¾, 1, 1¼, 1½, CONC. K.O.
D	2	½, ¾, 1, 1¼ CONC. K.O.
E	1	¾, 1, 1¼, 1½, 2 CONC. K.O.




Version:

1

**All dimensions are +/- 1/16".
Drawing views are not to scale.**

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

U5934-XL-BLG



Catalog Number	U5934-XL-BLG
Marketing Product Description	4 Terminal Ringless Small Closing Plate 7-8 In Barrel Lock Ground With Bracket Provision
UPC	784572592278
Length (IN)	3.61
Width (IN)	8
Height (IN)	11.5
Brand Name	Milbank
Type	Ringless Meter Socket
Application	Meter Socket
Standard	UL Listed;Type 3R
Voltage Rating	600 Volts Alternating Current
Amperage Rating	100 Continuous Ampere
Phase	1 Phase
Frequency Rating	60 Hertz
Size	3.61L x 8W x 11.5H
Number Of Cutouts	0
Cutout Size	No Main Breaker
Cable Entry	Overhead or Underground
Terminal	Single Mechanical
Insulation	Glass Polyester
Mounting	Surface Mount

Enclosure G90 Galvanized Steel with Powder Coat Finish

Jaw Quantity 4 Terminal

Bypass Type No Bypass

Number of Meter Positions 1 Position

Equipment Ground Ground Bar

Hub Opening Small Closing Plate





Line Side Wire Range 12 - 1/0 AWG

Load Side Wire Range 12 - 1/0 AWG

Number Of Receptacles 0

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	6	U/L MNTG.EMBOSS
B	1	¼ SOLID K.O.
C	3	¾, 1, 1¼, 1½, CONC. K.O.
D	2	½, ¾, 1, 1¼ CONC. K.O.
E	1	¾, 1, 1¼, 1½, 2 CONC. K.O.



Version:

1

**All dimensions are +/- 1/16".
Drawing views are not to scale.**

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.