



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY528M 14.19" "Ty-Rap" Cable Tie

Abb Installation Products, Inc

Catalog Number	TY528M
Manufacturer	Abb Installation Products, Inc
Description	Cable Tie, Natural Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F) For Indoor Applications, UI/En/CSA62275 Type 2/21S Rated For Ah-2 Plenum or As A Flexible Cable and Conduit Support, Length Of 360.5MM (14.2 Inches), Width Of 4.82MM (0.19 Inches), Thickness Of 1.4MM (0.05 Inches), Tensile Strength Rating Of 222 Newtons (50 Pounds)
Weight per unit	0.0070 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	50
------------------	----

Dimensions and Weight

Length	14.2
Thickness	0.05
Width	0.19

Descriptions

Description	14.19" "TY-RAP" CABLE TIE
extra long description	ABB TY528M CBL TIE 50LB 14 NAT NYLO
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum or as a Flexible Cable and Conduit Support, Length of 360.5mm (14.2 Inches), Width of 4.82mm (0.19 Inches), Thickness of 1.4mm (0.05 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)
Product Type	CBL Tie 50LB 14 Nat Nylon 2-PC D
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210805139
Manufacturers Part Number	TY528M
UPC	786210805139



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE

Packaging

Carton	100
Package	500
Weight Per each	0.007

Uses, Certifications, and Standards

standard	UL E49405
----------	-----------