

# Specifications

## Eaton UAT4R2352UFLCH



Photo is representative

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #1/0-500 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

### General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UAT4R2352UFLCH
UPC	782116997831
PRODUCT LENGTH/DEPTH	5.375 in
PRODUCT HEIGHT	14.125 in
PRODUCT WIDTH	40.625 in
PRODUCT WEIGHT	49 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	FMG approved



### Product specifications

TYPE	Multiple position residential
------	-------------------------------

### Resources

	service
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
<b>LINE</b>	#1/0-500 kcmil
<b>LOAD</b>	#8-250 kcmil
<b>ENCLOSURE MATERIAL</b>	Aluminum
<b>NUMBER OF WIRES</b>	Three-wire
<b>CONNECTION</b>	Ground connection
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF SOCKETS</b>	4

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UAT4R2352UFLCH</a>
<b>WARRANTY GUIDES</b>	<a href="#">Selling Policy 25-000 - Distribution and Control Products and Services</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.



# Specifications

## Eaton UAT4R2352UFLCH



Photo is representative

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #1/0-500 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

### General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UAT4R2352UFLCH
UPC	782116997831
PRODUCT LENGTH/DEPTH	5.375 in
PRODUCT HEIGHT	14.125 in
PRODUCT WIDTH	40.625 in
PRODUCT WEIGHT	49 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	FMG approved



### Product specifications

TYPE	Multiple position residential
------	-------------------------------

### Resources

	service
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
<b>LINE</b>	#1/0-500 kcmil
<b>LOAD</b>	#8-250 kcmil
<b>ENCLOSURE MATERIAL</b>	Aluminum
<b>NUMBER OF WIRES</b>	Three-wire
<b>CONNECTION</b>	Ground connection
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF SOCKETS</b>	4

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UAT4R2352UFLCH</a>
<b>WARRANTY GUIDES</b>	<a href="#">Selling Policy 25-000 - Distribution and Control Products and Services</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

