



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY5354M Locking Cable Tie

Abb Installation Products, Inc

Catalog Number	TY5354M
Manufacturer	Abb Installation Products, Inc
Description	Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F) For Indoor Applications, Length Of 198MM (7.8 Inches), Width Of 4.6MM (0.18 Inch), Thickness Of 1MM (0.04 Inches), Tensile Strength Rating Of 222 Newtons (50 Pounds), #10 Screw For Mounting
Weight per unit	0.0100 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	50;222
------------------	--------

Dimensions and Weight

Length	7.800000000000000
Thickness	0.040000000000000
Width	0.180000000000000

Descriptions

Description	LOCKING CABLE TIE
extra long description	ABB TY5354M CBL TIE 50LB 14 NAT NO1
Long Description	Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 198mm (7.8 Inches), Width of Width of 4.6mm (0.18 Inch), Thickness of 1mm (0.04 Inches), Tensile Strength Rating of 222 Newtons (50 pounds), #10 Screw for Mounting
Product Type	CBL Tie 50LB 14 Nat NO10 MTG Hole
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210886374
Manufacturers Part Number	TY5354M
UPC	786210886374

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Integrated Mounting Hole



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 100

Packaging

Carton 100

Package 500

Weight Per each 0.01