

Eaton UBTH4330TCH

Catalog Number: UBTH4330TCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub open, 3/8 inch stud, 4-jaw, 1-ph, 3/8 inch stud, Barrel lock, Lever bypass, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UBTH4330TCH

UPC

786685135472

Product Length/Depth

5.69 in

Product Height

36.63 in

Product Width

15 in

Product Weight

38 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Special features

Barrel lock provisions

Type

Single-position commercial or residential service

Amperage Rating

320A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

TN : Nashville Electric Service

Line

3/8 in stud

Load

3/8 in stud

Number of wires

Three-wire

Hub type

5 x 5 hub opening

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

Single Meter Sockets

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT 320A 1P HO

Specifications and datasheets

Metering Equipment - Utilities Servicing Upstate New York

Eaton Specification Sheet - UBTH4330TCH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton UBTH4330TCH

Catalog Number: UBTH4330TCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub open, 3/8 inch stud, 4-jaw, 1-ph, 3/8 inch stud, Barrel lock, Lever bypass, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UBTH4330TCH

UPC

786685135472

Product Length/Depth

5.69 in

Product Height

36.63 in

Product Width

15 in

Product Weight

38 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Special features

Barrel lock provisions

Type

Single-position commercial or residential service

Amperage Rating

320A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

TN : Nashville Electric Service

Line

3/8 in stud

Load

3/8 in stud

Number of wires

Three-wire

Hub type

5 x 5 hub opening

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

Single Meter Sockets

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT 320A 1P HO

Specifications and datasheets

Metering Equipment - Utilities Servicing Upstate New York

Eaton Specification Sheet - UBTH4330TCH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia