

# Specifications

## Eaton U17

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1/2"



Photo is representative

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	U17
<b>UPC</b>	662276465800
<b>PRODUCT LENGTH/DEPTH</b>	7.13 in
<b>PRODUCT HEIGHT</b>	3.69 in
<b>PRODUCT WIDTH</b>	1.5 in
<b>PRODUCT WEIGHT</b>	1.55 lb



### Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous

### Product specifications

**SHAPE** U

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	3 4 12

<b>TRADE SIZE</b>	1/2"
<b>MATERIAL</b>	Feraloy iron alloy

## Resources

### 3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds U17 3D drawing](#)

### CATALOGS

[Crouse-Hinds series Form 7 catalog page](#)

### CERTIFICATION REPORTS

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

### INSTALLATION INSTRUCTIONS

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - U17](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

### TECHNICAL SERVICE BULLETINS

[Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

## Eaton U17

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1/2"



Photo is representative

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	U17
<b>UPC</b>	662276465800
<b>PRODUCT LENGTH/DEPTH</b>	7.13 in
<b>PRODUCT HEIGHT</b>	3.69 in
<b>PRODUCT WIDTH</b>	1.5 in
<b>PRODUCT WEIGHT</b>	1.55 lb



### Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous

### Product specifications

**SHAPE** U

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	3 4 12

<b>TRADE SIZE</b>	1/2"
<b>MATERIAL</b>	Feraloy iron alloy

## Resources

**3D CAD DRAWING PACKAGE** [Eaton Crouse-Hinds U17 3D drawing](#)

**CATALOGS** [Crouse-Hinds series Form 7 catalog page](#)

**CERTIFICATION REPORTS** [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

**INSTALLATION INSTRUCTIONS** [IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - U17](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

**TECHNICAL SERVICE BULLETINS** [Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

