



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UAG12500 1/2" Ua Sealtite Conduit, Bonded UI 500' *Southwire Company*

Catalog Number	UAG12500
Manufacturer	Southwire Company
Description	UI Liquid-Tuff™ Liquidtight Conduit, Type LFMC, 6200 Series, Liquidtight Flexible Metal Conduit. Hot Dipped Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1/2 Inch Diameter, 500 Foot Reel
Weight per unit	0.3000 (lbs/ft)
Product Category	Flexible Metallic Conduit

Features

Inside Diameter	0.622/0.642
Material	Steel
outside diameter	0.820/0.840

Material, Color, and Finish

Color	Gray
Finish	PVC
Jacket Material	PVC

Dimensions and Weight

Length	500
--------	-----

Descriptions

Description	1/2" UA SEALTITE CONDUIT, BONDED UL 500'
extra long description	AFC 6202-45-00 1/2" UL LT LFMC GRA
Features	UL LIQUIDTUFF™ Liquidtight Flexible Steel Conduit designed for use as a raceway for power, control and communication cables in accordance with Article 350 of the National Electrical Code.
Long Description	UL LIQUID-TUFF™ Liquidtight Conduit, Type LFMC, 6200 Series, Liquidtight Flexible Metal Conduit. Hot Dipped Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1/2 inch Diameter, 500 Foot Reel
Product Type	1/2" UI LT LFMC Gray 500' RL
Short Description	1/2" UL LT LFMC GRAY 500' RL
Special Features	UL bonded strip 3/8in - 1.25in for grounding. UL Liquidtight all sizes. Sunlight resistant. Flame retardant PVD jacket. Hot dipped zinc galvanized steel low carbon steel core.

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680119988
Manufacturers Part Number	55082605
UPC	077680119988



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquidtight Flexible Metal Conduit

Trade Size

Trade Size	1/2
------------	-----

Packaging

Carton	500
Weight	0.31
Weight Per foot	0.3

Uses, Certifications, and Standards

Application	For Service Entrance Wiring Upto 6 FT
Temperature Rating	176