

Eaton UASTS131C226CH

Catalog Number: UASTS131C226CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, 13-jaw, 3-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 4-wire, Ringless, 600 Vac



Photo is representative

General specifications

Product Name

Eaton meter socket

Catalog Number

UASTS131C226CH

UPC

786685216409

Product Length/Depth

4.35 in

Product Height

20 in

Product Width

12 in

Product Weight

18 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Instrument rated socket

Amperage Rating

20A

Feed type

Top/bottom

Number of jaws

13-jaw

Phase

Three-phase

Enclosure material

Aluminum

Number of wires

Four-wire

Hub type

3-5/16 in hub cover plate

Security

Ringless

Voltage rating

600 V

Accessories

Factory wired test switch

Number of sockets

1

Resources

Specifications and datasheets

[Eaton Specification Sheet - UASTS131C226CH](#)

Eaton UASTS131C226CH

Catalog Number: UASTS131C226CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, 13-jaw, 3-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 4-wire, Ringless, 600 Vac



Photo is representative

General specifications

Product Name

Eaton meter socket

Catalog Number

UASTS131C226CH

UPC

786685216409

Product Length/Depth

4.35 in

Product Height

20 in

Product Width

12 in

Product Weight

18 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Instrument rated socket

Amperage Rating

20A

Feed type

Top/bottom

Number of jaws

13-jaw

Phase

Three-phase

Enclosure material

Aluminum

Number of wires

Four-wire

Hub type

3-5/16 in hub cover plate

Security

Ringless

Voltage rating

600 V

Accessories

Factory wired test switch

Number of sockets

1

Resources

Specifications and datasheets

[Eaton Specification Sheet - UASTS131C226CH](#)