

# Eaton UAT4R2352UFLCH

Catalog Number: UAT4R2352UFLCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #1/0-500 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

## General specifications



Photo is representative

### Product Name

Eaton meter socket

### UPC

782116997831

### Product Height

14.125 in

### Product Weight

49 lb

### Certifications

UL Listed

### Catalog Number

UAT4R2352UFLCH

### Product Length/Depth

5.375 in

### Product Width

40.625 in

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Catalog Notes

FMG approved

## Product specifications

### Type

Multiple position residential service

### Amperage Rating

200A

### Feed type

Top/bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

### Line

#1/0-500 kcmil

### Load

#8-250 kcmil

### Enclosure material

Aluminum

### Number of wires

Three-wire

### Connection

Ground connection

### Security

Ringless

### Voltage rating

600 V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - UAT4R2352UFLCH](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Number of sockets

4



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton UAT4R2352UFLCH

Catalog Number: UAT4R2352UFLCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #1/0-500 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

## General specifications



Photo is representative

### Product Name

Eaton meter socket

### UPC

782116997831

### Product Height

14.125 in

### Product Weight

49 lb

### Certifications

UL Listed

### Catalog Number

UAT4R2352UFLCH

### Product Length/Depth

5.375 in

### Product Width

40.625 in

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Catalog Notes

FMG approved

## Product specifications

### Type

Multiple position residential service

### Amperage Rating

200A

### Feed type

Top/bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

### Line

#1/0-500 kcmil

### Load

#8-250 kcmil

### Enclosure material

Aluminum

### Number of wires

Three-wire

### Connection

Ground connection

### Security

Ringless

### Voltage rating

600 V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - UAT4R2352UFLCH](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Number of sockets

4



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)