



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



URTRS101BE 125A 1PH Ring Style Meter Socket Small Hub Opening

Eaton Corp

Catalog Number	URTRS101BE
Manufacturer	Eaton Corp
Description	Eaton Meter Socket, 3 5/16 In Hub Opening, 125A, Overhead, Hub Opening, #8-2/0 Kcmil, Four-Jaw, Single-Phase, #8-2/0 Kcmil, Sockets:1, Three-Wire, Ring, 600V
Weight per unit	7.0 (lbs/each)
Product Category	Residential Single Meter Socke

Features

amperage rating	125A
dimensions	3.6300 IN X 8.2500 IN X 11.0000 IN
Phase	Single-phase
Voltage Rating	600 V

Descriptions

Also Known As...	Meter Socket Meter Box
Description	125A 1PH RING STYLE METER SOCKET SMALL HUB OPENING
extra long description	ETN URTRS101BE MtrSkt,125A, Ring,4-J
Features	Eaton is your one-stop shop for the widest range of residential and light commercial electric meter sockets in the industry. These single-socket surface- or flush-mount outdoor enclosures come in two styles, allowing for both easy, cost-saving installation, and for the use of BR- or CH-type branch breakers. The one-piece, die-run electric meter socket enclosures eliminate tampering and extend product life. These are utility approved and can be used for residential meter socket installations, rural service
Long Description	Eaton meter socket, 3 5/16 in hub opening, 125A, Overhead, Hub opening, #8-2/0 kcmil, Four-jaw, Single-phase, #8-2/0 kcmil, Sockets:1, Three-wire, Ring, 600V
Product Type	MTRSKT, 125A, Ring, 4-Jaw, Oh

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685217826
Manufacturers Part Number	URTRS101BE
UPC	786685217826

Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Meter socket



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	7

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	UL Listed