

# Specifications



## Eaton UHTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-ph, #8-2/0 AWG, Horn bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UHTRS101BE
<b>UPC</b>	786685217734
<b>PRODUCT LENGTH/DEPTH</b>	3.61 in
<b>PRODUCT HEIGHT</b>	11.05 in
<b>PRODUCT WIDTH</b>	8.22 in
<b>PRODUCT WEIGHT</b>	6.7 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Single-position residential service
<b>AMPERAGE RATING</b>	125A
<b>FEED TYPE</b>	Overhead
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	NY : Central Hudson Gas & Electric (CHG&E) OH : Dayton Power and Light (DP&L) MD : First Energy (Potomac Edison) VA : First Energy (Potomac Edison) WV : First Energy (Mon Power) NJ : First Energy (Jersey Central Power and Light) OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company) PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power) WI : Madison Gas and Electric (MGE) IN : Northern Indiana Public Service Company (NIPSCO) WI : WE Energies / Wisconsin Public Service (WPS) NY : Rochester Gas & Electric (RG&E) NY : New York State Electric & Gas (NYSEG)
<b>LINE</b>	#8-2/0 AWG
<b>LOAD</b>	#8-2/0 AWG
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	3-5/16 in hub opening
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>BYPASS</b>	Horn
<b>NUMBER OF SOCKETS</b>	1

## Resources

### CATALOGS

[Residential and Light Commercial Metering Products, Volume 1 Tab 4](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UHTRS101BE](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

