ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



USB20ACW Recp Duplex 20A125V 3.1A5V Usb Port Ac W

Hubbell Incorporated Delaware

Catalog Number	USB20ACW
Manufacturer	Hubbell Incorporated Delaware
Description	Usb Charger Duplex Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, 1) 3.1 A "C" Usb and "A" Ports, White
Weight per unit	0.3000 (lbs/each)
Product Category	Wiring Devices

Features

amperage rating	20
connection	Back Wire Screws
Dielectric Strength	1500 V Withstand
insulation	False
Material	COMPOSITE
Number of Wires	3-Wire
pallet quantity	2700
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	1815
Wire Size	#14-10

Dimensions and Weight

Size	Standard Sized Product

Descriptions

Description	RECP DUPLEX 20A125V 3.1A5V USB PORT AC W
extra long description	HWDK USB20ACW RCPT DUP 20A125V 3.1A
Features	More ways to charge faster with Hubbell's line of USB chargers, available in Type C, Type A&C or the legacy Type A, all with a USB power output from 2 to 5 amps. Hubbell's USB charger duplex receptacle provides both USB and electrical power in a standard single gang opening. Designed to provide maximum charging for portable electronics, the USB ports are capable of charging two tablets simultaneously. The 4 port charger outlets feature a USB port door, which enables power when open. When closed, all power
Long Description	USB Charger Duplex Receptacle, 20A 125V,2-Pole 3-Wire Grounding, 5-20R, 1) 3.1 A "C" USB and "A" Ports, White
Product Type	RCPT Dup 20A125V 3.1A5V Usb Port Ac W
Special Features	3.1 A 5V DC, Style A and C

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00883778310119
Manufacturers Part Number	USB20ACW
series	Hubbell-PRO
UPC	883778310119

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	USB

Packaging

Carton	1
Package	10
Weight Per each	0.3

Uses, Certifications, and Standards

Application	USB Charging/Power
environmental conditions	Indoor Dry unless protected by additional means
nema rating	5-20R
standard	cULus Listed to UL498, UL1310