

Specifications

Eaton UT4R1121BCH

Eaton meter socket, Multi position commercial or resi service, 100A, Over/under, 3-5/16 inch hub open, #6-250 kcmil, Four-jaw, 1-ph, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UT4R1121BCH
UPC	782116094639
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	14.13 in
PRODUCT WIDTH	40.63 in
PRODUCT WEIGHT	40 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Multiple position commercial or residential service
AMPERAGE RATING	100A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	ME : Central Maine Power ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company) SC : South Carolina Electric and Gas (SCE&G) AR : Entergy LA : Entergy MS : Entergy TX : Entergy
LINE	#6-250 kcmil
LOAD	#8-2/0 AWG

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UT4R1121BCH
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub opening
SECURITY	Ringless
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	4

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton UT4R1121BCH

Eaton meter socket, Multi position commercial or resi service, 100A, Over/under, 3-5/16 inch hub open, #6-250 kcmil, Four-jaw, 1-ph, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UT4R1121BCH
UPC	782116094639
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	14.13 in
PRODUCT WIDTH	40.63 in
PRODUCT WEIGHT	40 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Multiple position commercial or residential service
AMPERAGE RATING	100A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	ME : Central Maine Power ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company) SC : South Carolina Electric and Gas (SCE&G) AR : Entergy LA : Entergy MS : Entergy TX : Entergy
LINE	#6-250 kcmil
LOAD	#8-2/0 AWG

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UT4R1121BCH
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub opening
SECURITY	Ringless
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	4

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

