

# Eaton UT4R1121BCH

Catalog Number: UT4R1121BCH

Eaton meter socket, Multi position commercial or resi service, 100A, Over/under, 3-5/16 inch hub open, #6-250 kcmil, Four-jaw, 1-ph, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

## General specifications



### Product Name

Eaton meter socket

### Catalog Number

UT4R1121BCH

### UPC

782116094639

### Product Length/Depth

4.5 in

### Product Height

14.13 in

### Product Width

40.63 in

### Product Weight

40 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Multiple position commercial or residential service

### Amperage Rating

100A

### Feed type

Top/bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

ME : Central Maine Power

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

SC : South Carolina Electric and Gas (SCE&G)

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

### Line

#6-250 kcmil

### Load

#8-2/0 AWG

### Number of wires

Three-wire

### Hub type

3-5/16 in hub opening

### Security

Ringless

### Voltage rating

600 V

### Number of sockets

4

## Resources

### Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

### Specifications and datasheets

[Eaton Specification Sheet - UT4R1121BCH](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton UT4R1121BCH

Catalog Number: UT4R1121BCH

Eaton meter socket, Multi position commercial or resi service, 100A, Over/under, 3-5/16 inch hub open, #6-250 kcmil, Four-jaw, 1-ph, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

## General specifications



### Product Name

Eaton meter socket

### Catalog Number

UT4R1121BCH

### UPC

782116094639

### Product Length/Depth

4.5 in

### Product Height

14.13 in

### Product Width

40.63 in

### Product Weight

40 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Multiple position commercial or residential service

### Amperage Rating

100A

### Feed type

Top/bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

ME : Central Maine Power

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

SC : South Carolina Electric and Gas (SCE&G)

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

### Line

#6-250 kcmil

### Load

#8-2/0 AWG

### Number of wires

Three-wire

### Hub type

3-5/16 in hub opening

### Security

Ringless

### Voltage rating

600 V

### Number of sockets

4

## Resources

### Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

### Specifications and datasheets

[Eaton Specification Sheet - UT4R1121BCH](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)