

Specifications



Eaton UTE7213CCH

Eaton meter socket, Comm, 200A, Over/under, 3-5/16 inch hub cover plate, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac

Product specifications

TYPE	Commercial
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Seven-jaw
PHASE	Three-phase
UTILITY APPROVALS	WI : WE Energies / Wisconsin Public Service (WPS)

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTE7213CCH
UPC	786685351247
PRODUCT LENGTH/DEPTH	4.94 in
PRODUCT HEIGHT	19 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	25 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Four-wire
HUB TYPE	3-5/16 in hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1



Specifications



Eaton UTE7213CCH

Eaton meter socket, Comm, 200A, Over/under, 3-5/16 inch hub cover plate, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac

Product specifications

TYPE	Commercial
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Seven-jaw
PHASE	Three-phase
UTILITY APPROVALS	WI : WE Energies / Wisconsin Public Service (WPS)

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTE7213CCH
UPC	786685351247
PRODUCT LENGTH/DEPTH	4.94 in
PRODUCT HEIGHT	19 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	25 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Four-wire
HUB TYPE	3-5/16 in hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

