

Specifications

Eaton UTE7213TCH

Eaton meter socket, Comm, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd con (#14-#2 Cu), Triplex, Four-wire, Ringless, 600 Vac



General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTE7213TCH
UPC	786685351261
PRODUCT LENGTH/DEPTH	4.94 in
PRODUCT HEIGHT	19 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	25 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed



Powering Business Worldwide

Product specifications

TYPE	Commercial
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Seven-jaw
PHASE	Three-phase
UTILITY APPROVALS	NY : Central Hudson Gas & Electric (CHG&E) ME : Central Maine Power OH : Dayton Power and Light (DP&L) MD : First Energy (Potomac Edison) VA : First Energy (Potomac Edison) WV : First Energy (Mon Power) NJ : First Energy (Jersey Central Power and Light) OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company) PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power) WI : WE Energies / Wisconsin Public Service (WPS) SC : South Carolina Electric and Gas (SCE&G) TX : Entergy NM : Texas-New Mexico Power (TNMP) TX : Texas-New Mexico Power (TNMP)
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Four-wire
HUB TYPE	5 x 5 hub opening
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTE7213TCH

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton UTE7213TCH

Eaton meter socket, Comm, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd con (#14-#2 Cu), Triplex, Four-wire, Ringless, 600 Vac



General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTE7213TCH
UPC	786685351261
PRODUCT LENGTH/DEPTH	4.94 in
PRODUCT HEIGHT	19 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	25 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed



Powering Business Worldwide

Product specifications

TYPE	Commercial
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Seven-jaw
PHASE	Three-phase
UTILITY APPROVALS	NY : Central Hudson Gas & Electric (CHG&E) ME : Central Maine Power OH : Dayton Power and Light (DP&L) MD : First Energy (Potomac Edison) VA : First Energy (Potomac Edison) WV : First Energy (Mon Power) NJ : First Energy (Jersey Central Power and Light) OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company) PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power) WI : WE Energies / Wisconsin Public Service (WPS) SC : South Carolina Electric and Gas (SCE&G) TX : Entergy NM : Texas-New Mexico Power (TNMP) TX : Texas-New Mexico Power (TNMP)
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Four-wire
HUB TYPE	5 x 5 hub opening
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTE7213TCH

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

