



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNY215 3/4" to 1/2" Male Union

Crouse-Hinds

Catalog Number	UNY215
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Uny Union, Rigid/Imc, Male, Steel, Group B Rated, 1/2" Female to 3/4" Male
Weight per unit	0.6800 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	2.6300 IN X 1.8800 IN X 1.8800 IN

Descriptions

Description	3/4" TO 1/2" MALE UNION
extra long description	CRS-H UNY215 1/2 FEMALE TO 3/4 MALE
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series UNY union, Rigid/IMC, Male, Steel, Group B rated, 1/2" female to 3/4" male
Product Type	1/2 Female to 3/4 Male NPT Uny Union
Special Features	1-13/16 In Diameter X 2-7/16 In Length

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274648002
Manufacturers Part Number	UNY215
UPC	782274648002

Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	Union

Packaging

Carton	1
Package	10
Weight Per each	0.68



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2
	Group F G, Class III
standard	UL 886, CSA C22.2