

Specifications

Eaton UTRS223AFLCH



Photo is representative

Eaton meter socket, 1-pos resi service, 200A, Under, Solid top, 4-jaw, 1-ph, #8-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTRS223AFLCH
UPC	786680191541
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	5 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	14 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	Offset design with lugs facing downward for bottom service cable entry only, Bangor Hydro, CMP, CLECO, Duke PC, ENTERGY, Louisiana & Light, TX NM, Middle Tennessee, NSTAR, Potomac, Otter Tail, Rural, Public Service of NM & City of Farm



Product specifications

SPECIAL FEATURES

MEG Approved

Resources

TYPE	Single-position residential service
AMPERAGE RATING	200A
FEED TYPE	Bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase

UTILITY APPROVALS

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 FL : Tallahassee City Electric

LINE	#8-350 kcmil
LOAD	#8-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	Solid top
SECURITY	Ringless
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UTRS223AFLCH](#)

WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton UTRS223AFLCH



Photo is representative

Eaton meter socket, 1-pos resi service, 200A, Under, Solid top, 4-jaw, 1-ph, #8-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTRS223AFLCH
UPC	786680191541
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	5 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	14 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	Offset design with lugs facing downward for bottom service cable entry only, Bangor Hydro, CMP, CLECO, Duke PC, ENTERGY, Louisiana & Light, TX NM, Middle Tennessee, NSTAR, Potomac, Otter Tail, Rural, Public Service of NM & City of Farm



Product specifications

SPECIAL FEATURES

MEG Approved

Resources

TYPE	Single-position residential service
AMPERAGE RATING	200A
FEED TYPE	Bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase

UTILITY APPROVALS

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
 FL : Tallahassee City Electric

LINE	#8-350 kcmil
LOAD	#8-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	Solid top
SECURITY	Ringless
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UTRS223AFLCH](#)

WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

