

Eaton URTRS223ACH

Catalog Number: URTRS223ACH

Eaton meter socket, Solid top, 200A, Underground, Solid top, #8-350 kcmil, Four-jaw, Single-phase, #8-350 kcmil, Sockets:1, Three-wire, Ring, 600V

General specifications



Product Name

Eaton meter socket

Catalog Number

URTRS223ACH

UPC

786685125428

Product Length/Depth

4.93 in

Product Height

13 in

Product Width

13 in

Product Weight

13 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Solid top

Amperage Rating

200A

Feed type

Bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

TN : Knoxville Utility Board (KUB)

Line

#8-350 kcmil

Load

#8-350 kcmil

Number of wires

Three-wire

Hub type

Solid top

Security

Ring

Voltage rating

600 V

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Specifications and datasheets

[Eaton Specification Sheet - URTRS223ACH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton URTRS223ACH

Catalog Number: URTRS223ACH

Eaton meter socket, Solid top, 200A, Underground, Solid top, #8-350 kcmil, Four-jaw, Single-phase, #8-350 kcmil, Sockets:1, Three-wire, Ring, 600V

General specifications



Product Name

Eaton meter socket

Catalog Number

URTRS223ACH

UPC

786685125428

Product Length/Depth

4.93 in

Product Height

13 in

Product Width

13 in

Product Weight

13 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Solid top

Amperage Rating

200A

Feed type

Bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

TN : Knoxville Utility Board (KUB)

Line

#8-350 kcmil

Load

#8-350 kcmil

Number of wires

Three-wire

Hub type

Solid top

Security

Ring

Voltage rating

600 V

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Specifications and datasheets

[Eaton Specification Sheet - URTRS223ACH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)