Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



USB20ACBK Recp Duplex 20A125V 3.1A5V Usb Port Ac BK

Hubbell Incorporated Delaware

Catalog Number	USB20ACBK
Manufacturer	Hubbell Incorporated Delaware
Description	Usb Charger Duplex Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, 1) 3.1 A "C" Usb and "A" Ports, Black
Weight per unit	0.3000 (lbs/each)
Product Category	Wiring Devices

Features

amperage rating	20
connection	Back Wire Screws
Dielectric Strength	1500 V Withstand
insulation	False
Material	COMPOSITE
Number of Wires	3-Wire
pallet quantity	3500
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	1815
Wire Size	#14-10

Dimensions and Weight

Size	Standard Sized Product

Descriptions

Description	RECP DUPLEX 20A125V 3.1A5V USB PORT AC BK
extra long description	HWDK USB20ACBK RCPT DUP 20A125V 3.1
Features	More ways to charge faster with Hubbell's line of USB chargers, available in Type C, Type A&C or the legacy Type A, all with a USB power output from 2 to 5 amps. Hubbell's USB charger duplex receptacle provides both USB and electrical power in a standard single gang opening. Designed to provide maximum charging for portable electronics, the USB ports are capable of charging two tablets simultaneously. The 4 port charger outlets feature a USB port door, which enables power when open. When closed, all power
Long Description	USB Charger Duplex Receptacle, 20A 125V,2-Pole 3-Wire Grounding, 5-20R, 1) 3.1 A "C" USB and "A" Ports, Black
Product Type	RCPT Dup 20A125V 3.1A5V Usb Port Ac BK
Special Features	3.1 A 5V DC, Style A and C

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00883778310140
Manufacturers Part Number	USB20ACBK
series	Hubbell-PRO
UPC	883778310140

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	One Type A, One Type-C USB Port

Packaging

Carton	1
Package	10
Weight Per each	0.3

Uses, Certifications, and Standards

Application	USB Charging/Power
environmental conditions	Indoor Dry unless protected by additional means
nema rating	5-20R
standard	cULus Listed to UL498, UL1310