

Eaton UTRS213BE

Catalog Number: UTRS213BE

Eaton meter socket, 1-pos resi service, 200 A, Over/under, 3-5/16 inch hub open, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTRS213BE

UPC

786685217758

Product Length/Depth

4.48 in

Product Height

15.11 in

Product Width

11.22 in

Product Weight

14 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Single-position residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

ME : Central Maine Power

MI : DTE Energy (Detroit Edison)

MO : Empire District Electric

OK : Empire District Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

TN : Knoxville Utility Board (KUB)

TX : Oncor

NM : Public Service Company of New Mexico (PNM)

CT : United Illuminating (UI)

SC : South Carolina Electric and Gas (SCE&G)

NM : Texas-New Mexico Power (TNMP)

TX : Texas-New Mexico Power (TNMP)

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Three-wire

Hub type

3-5/16 in hub opening

Security

Ringless

Voltage rating

600 V

Resources

Brochures

[Single Meter Sockets](#)

Drawings

[Dimensional Drawing - METER SOCKET UTRS213\(X\)E, UGTRS213\(X\)E 200AMP, 1 \$\phi\$ OH/UG, RINGLESS STYLE](#)

Specifications and datasheets

[Eaton Specification Sheet - UTRS213BE](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Number of sockets

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton UTRS213BE

Catalog Number: UTRS213BE

Eaton meter socket, 1-pos resi service, 200 A, Over/under, 3-5/16 inch hub open, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTRS213BE

UPC

786685217758

Product Length/Depth

4.48 in

Product Height

15.11 in

Product Width

11.22 in

Product Weight

14 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Single-position residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

ME : Central Maine Power

MI : DTE Energy (Detroit Edison)

MO : Empire District Electric

OK : Empire District Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

TN : Knoxville Utility Board (KUB)

TX : Oncor

NM : Public Service Company of New Mexico (PNM)

CT : United Illuminating (UI)

SC : South Carolina Electric and Gas (SCE&G)

NM : Texas-New Mexico Power (TNMP)

TX : Texas-New Mexico Power (TNMP)

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Three-wire

Hub type

3-5/16 in hub opening

Security

Ringless

Voltage rating

600 V

Resources

Brochures

[Single Meter Sockets](#)

Drawings

[Dimensional Drawing - METER SOCKET UTRS213\(X\)E, UGTRS213\(X\)E 200AMP, 1 \$\phi\$ OH/UG, RINGLESS STYLE](#)

Specifications and datasheets

[Eaton Specification Sheet - UTRS213BE](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Number of sockets

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)