


Eaton UTRS233CCH

Catalog Number: UTRS233CCH

Eaton meter socket, 1-pos resi service, 200A, Over/under, 3-5/16 inch hub cover plate, #8-350 kcmil, 4-jaw, 1-ph, #8-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTRS233CCH

UPC

782116124039

Product Length/Depth

4.94 in

Product Height

17.13 in

Product Width

13 in

Product Weight

18 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Single-position residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

MO : Empire District Electric

OK : Empire District Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

GA : Georgia Power

Line

#8-350 kcmil

Load

#8-350 kcmil

Number of wires

Three-wire

Hub type

3-5/16 in hub cover plate

Security

Ringless

Voltage rating

600 V

Number of sockets

1

Resources

Brochures

Single Meter Sockets

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT 200A 1P HCP

Specifications and datasheets

Metering Equipment - Utilities Servicing Upstate New York

Eaton Specification Sheet - UTRS233CCH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.




Eaton.com/socialmedia

Eaton UTRS233CCH

Catalog Number: UTRS233CCH

Eaton meter socket, 1-pos resi service, 200A, Over/under, 3-5/16 inch hub cover plate, #8-350 kcmil, 4-jaw, 1-ph, #8-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTRS233CCH

UPC

782116124039

Product Length/Depth

4.94 in

Product Height

17.13 in

Product Width

13 in

Product Weight

18 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Single-position residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

MO : Empire District Electric

OK : Empire District Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

GA : Georgia Power

Line

#8-350 kcmil

Load

#8-350 kcmil

Number of wires

Three-wire

Hub type

3-5/16 in hub cover plate

Security

Ringless

Voltage rating

600 V

Number of sockets

1

Resources

Brochures

Single Meter Sockets

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT 200A 1P HCP

Specifications and datasheets

Metering Equipment - Utilities Servicing Upstate New York

Eaton Specification Sheet - UTRS233CCH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia