

Eaton UTTE4213UCH

Catalog Number: UTTE4213UCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Lever bypass, Two grounding conns (#14-#2 Cu), Quadplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name	Catalog Number
Eaton meter socket	UTTE4213UCH
UPC	Product Length/Depth
786685351322	4.94 in
Product Height	Product Width
19 in	13 in
Product Weight	Warranty
25 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed	Ameren, Union Electric, Central Illinois Public approved

defaultTaxonomyAttributeLabel

Type

Single-position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Ground

Quadplex

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Three-wire

Hub type

5 x 5 hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - SKT 200A 1P HCP](#)

Specifications and datasheets

[Eaton Specification Sheet - UTTE4213UCH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton UTTE4213UCH

Catalog Number: UTTE4213UCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Lever bypass, Two grounding conns (#14-#2 Cu), Quadplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name	Catalog Number
Eaton meter socket	UTTE4213UCH
UPC	Product Length/Depth
786685351322	4.94 in
Product Height	Product Width
19 in	13 in
Product Weight	Warranty
25 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed	Ameren, Union Electric, Central Illinois Public approved

defaultTaxonomyAttributeLabel

Type

Single-position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Ground

Quadplex

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Three-wire

Hub type

5 x 5 hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - SKT 200A 1P HCP](#)

Specifications and datasheets

[Eaton Specification Sheet - UTTE4213UCH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)