



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VGF20W 20A WHT Gfci RCPT

Eaton Wiring Devices

| | |
|------------------|--------------------------------|
| Catalog Number | VGF20W |
| Manufacturer | Eaton Wiring Devices |
| Description | Gfci Deco Duplex 20A 125V WH |
| Weight per unit | 0.5000 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|---|
| amperage rating | 20 A |
| connection | 4714 Lm |
| Material | Nylon Top Housing, Polycarbonate Bottom Housing |
| Poles | 2 Pole/ 3 Wire |
| Voltage Rating | 125 A |

Dimensions and Weight

| | |
|-------|--------|
| Width | 1.3 in |
|-------|--------|

Descriptions

| | |
|------------------|--|
| Description | 20A WHT GFCI RCPT |
| Long Description | GFCI Deco Duplex 20A 125V WH |
| Product Type | Gfci Deco Duplex 20A 125V WH |
| Special Features | Hospital Grade, Tamper Resistant, Wiring Type Back and Side Wire, With Standard Size Unbreakable Wallplate |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | COOPER WIRING DEVICES |
| GTIN | 00032664657870 |
| Manufacturers Part Number | VGF20W |
| sub brand | Arrow Hart |
| UPC | 032664657870 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------------|
| Category Description | Residential GFCI devices |
| Type | Hospital,GFCI,Back And Side Wire |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.5 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|--------------------------------------|
| Application | Hospital grade |
| Enclosure | Hospital Grade Tamper Reistant |