



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## WF6AL020SWW590MV 6" Led Wafer Lumen SLCT 27K/3K/35K/4K/5K 120/277V

*Lithonia Lighting - Acuity*



|                  |   |
|------------------|---|
| Catalog Number   | WF6AL020SWW590MV  |
| Manufacturer     | Lithonia Lighting - Acuity  |
| Description      | The 6IN Canless Wafer Downlight Has An Innovative, Slim Design That Installs Quickly and Easily Into As Little As 3IN Of Plenum Space Allowing For It to Fit Into Ceiling Spaces Where Most Traditional Recessed Housings Do Not. Wafers Install Directly Into Dry Wall Eliminating The Need For Recessed Housings. Once Installed, Our Wafer Provides An All-In-One Design Featuring Switchable White Color Temperature and Adjustable Lumen Output Technology. This Technology Gives The Ultimate In Flexibility, Providing Y |
| Weight per unit  | 1.4 (lbs/each)  |
| Product Category | Lighting  |

### Features

|                               |                        |
|-------------------------------|------------------------|
| average life                  | 50,000                 |
| dimnable                      | Yes                    |
| Hardware                      | Yes                    |
| Lamp Included                 | Yes                    |
| Lamp Type                     | LED - Dynamic          |
| lumens                        | 1050 LM,1300 LM,800 LM |
| Material                      | Aluminum               |
| Maximum Operating Temperature | 25                     |
| Number of Lamps               | 1                      |
| Power Source                  | Hardwired              |
| Shape                         | Round                  |
| Voltage Rating                | 120-277                |
| Warranty                      | 3                      |
| Wattage                       | 16                     |

### Material, Color, and Finish

|                             |  |
|-----------------------------|--|
| Color                       | White                                  |
| color rendering index (cri) | 90                                     |
| color temperature           | 2700 ,3000 ,3500 ,4000 ,5000 ,Variable |
| Finish                      | Matte                                  |
| Lens Color                  | WHITE                                  |
| Lens Material               | Polycarbonate                          |
| Style                       | CONTEMPORARY                           |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Dimensions and Weight

|        |      |
|--------|------|
| Height | 1.25 |
| Length | 6.69 |
| Width  | 6.69 |

## Descriptions

|                        |   |
|------------------------|---|
| Construction           | Canless,New Construction,Remodel  |
| Description            | 6" LED WAFER LUMEN SLCT 27K/3K/35K/4K/5K 120/277V   |
| extra long description | LITH WF6 ALO20 SWW5 90CRI MVOLT MW  |
| Long Description       | The 6in Canless Wafer Downlight has an innovative, slim design that installs quickly and easily into as little as 3in of plenum space allowing for it to fit into ceiling spaces where most traditional recessed housings do not. Wafers install directly into dry wall eliminating the need for recessed housings. Once installed, our Wafer provides an all-in-one design featuring switchable white color temperature and adjustable lumen output technology. This technology gives the ultimate in flexibility, providing y |
| Product Type           | Downlight   |

## Manufacturer Information

|                           |                               |
|---------------------------|-------------------------------|
| Brand                     | JUNO                          |
| GTIN                      | 00197589217360                |
| Manufacturers Part Number | WF6 ALO20 SWW5 90CRI MVOLT MW |
| UPC                       | 197589217360                  |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
|----------------------|--|

## Trade Size

|               |      |
|---------------|------|
| aperture size | 6 in |
|---------------|------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 6    |
| Weight          | 1.23 |
| Weight Per each | 1.36 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Decorative,Hospitality,Residential,Retail                   |
| environmental conditions | Indoor,Outdoor  |
| Mounting                 | Recessed  |
| standard                 | CSAusCA Title 24,ENERGY STAR,FCC 47CFR Part 15 Consumer,JA8 |