



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1820 N Main St.
76033-0000, TX Cleburne
Phone: 817-202-8933
Fax: 817-202-8998



WGRB Wingtwistgrounding Connector, WGR Green, 250/Carton

Ideal

Catalog Number	WGRB
Manufacturer	Ideal
Description	Ideal WGR-B WGR Green Ground Cap 25
Weight per unit	0.0070 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

Material, Color, and Finish

Color	Green
-------	-------

Descriptions

Description	WINGTWISTGROUNDING CONNECTOR,WGR GREEN,250/CARTON
Features	With a full line for virtually every wire size and combination, the WingTwist Wire Connector offers a great combination of performance and value.The contoured wing design of the WingTwist provides maximum torque for a variety of electrical applications while the copolymer shell and live-action spring expand for smooth, progressive tightening providing dependable connections.With a tough, flame-retardant shell that withstands environmental extremes, and a long, deep skirt to provide maximum dielectric prote
Long Description	IDEAL WGR-B WGR GREEN GROUND CAP 25
Product Type	WGR Green Ground Cap 250 Box
Special Features	1,000V Maximum In Fixtures And Signs;Contoured Wing Design Provides Maximum Torque;Deep Skirt Protects Against Flash-Over;Expanding, Square-Wire Spring Creates Secure Connections;Features: Five Color-Coded Models Cover Common Construction Wire Ranges And Combinations, Including Grounding;Model Number: WGR

Manufacturer Information

Brand	Buchanan
GTIN	00781789470078
Manufacturers Part Number	WGR-B
UPC	781789470078

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
----------------------	-----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1820 N Main St.
76033-0000, TX Cleburne
Phone: 817-202-8933
Fax: 817-202-8998

Availability

Manufacturer Status	Inactive
minimum qty	250
Status	Inactive

Packaging

Carton	250
Weight Per each	0.007

Uses, Certifications, and Standards

Application	For Grounding And Bonding Applications
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 467 Listed, RoHS