



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **WAGS4010 #14-4/0 Wrap-Around Gel Splice Kit, 10" Length**

*Nsi Industries*

Catalog Number	WAGS4010
Manufacturer	Nsi Industries
Description	Easy-Splice Wrap Around Gel Splice Kit - #4/0 to 14 Awg - 10 Inch Easy-Splice Wrap-Around Gel Splice Closure Sleeves Quickly Insulate and Seal Buried Electrical Connections Rated Up to 1,000 Volts. Engineered to Handle Direct Burial and Manhole Applications, These Splice Enclosure Sleeves Are Equally Well Suited For Insulation and Jacket Repair. Simply Wrap and Snap The Sleeve On Any Cable In The Use Range. The Sealant Gel In The Sleeve Seals On Contact. The Splice Closure Sleeve Can Be Applied On All Comm
Weight per unit	0.4600 (lbs/each)
Product Category	Splicing & Terminating Kits

### **Features**

Cable Size	4/0-14 AWG
Cable Type	Class A-B
Voltage Rating	1000 V
Warranty	1 YEAR

### **Material, Color, and Finish**

Color	Black
-------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	#14-4/0 WRAP-AROUND GEL SPLICE KIT, 10" LENGTH
extra long description	NSI WAGS-4/0-10 Easy-Splice Wrap-Ar
Features	Easy-Splice Wrap Around Gel Splice Kit - #4/0 to 14 AWG - 10 Inch Easy-Splice wrap-around gel splice closure sleeves quickly insulate and seal buried electrical connections rated up to 1,000 volts. Engineered to handle direct burial and manhole applications, these splice enclosure sleeves are equally well suited for insulation and jacket repair. Simply wrap and snap the sleeve on any cable in the use range. The sealant gel in the sleeve seals on contact. The splice closure sleeve can be applied on all comm
Long Description	Easy-Splice Wrap Around Gel Splice Kit - #4/0 to 14 AWG - 10 Inch Easy-Splice wrap-around gel splice closure sleeves quickly insulate and seal buried electrical connections rated up to 1,000 volts. Engineered to handle direct burial and manhole applications, these splice enclosure sleeves are equally well suited for insulation and jacket repair. Simply wrap and snap the sleeve on any cable in the use range. The sealant gel in the sleeve seals on contact. The splice closure sleeve can be applied on all comm
Product Type	Easy-Splice Wrap-Around 4/0 10"
Special Features	Wrap Around Gel Splice For Fast Installation - 10 Sleeve Length

## Manufacturer Information

Brand	NSi
GTIN	00662381015709
Manufacturers Part Number	WAGS-4/0-10
UPC	662381015709

## Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
Type	Wrap Around Gel Splice Kits

## Packaging

Carton	3
Weight Per each	0.46

## Uses, Certifications, and Standards

Application	Splicing Wire
Operating Temperature standard	-40 C To 90 C ANSI C119.1-1986 Qualified