



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF4SWW590CRIMBM6 4" 9W Led Wafer 27K/3K/35K/4K/5K Black 90cri *Lithonia Lighting - Acuity*

| | |
|------------------|--|
| Catalog Number | WF4SWW590CRIMBM6 |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | The Wafer™ Led Downlights With Switchable White Technology Provides High-Quality Light Output and Efficiency and Features A Switch For Easy Color Temperature Adjustment While Eliminating The Need For Recessed Housings. |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-------------------------------|-----------------|
| average life | 50,000 |
| dimensions | 4.7 x 1.1 x 1.1 |
| dimnable | Yes |
| Hardware | Yes |
| Lamp Included | Yes |
| Lamp Type | LED - Dynamic |
| lumens | 670 LM |
| Material | Aluminum |
| Maximum Operating Temperature | 25 |
| Number of Lamps | 1 |
| Power Source | Hardwired |
| Shape | Round |
| Voltage Rating | 120 |
| Warranty | 3 |
| Wattage | 9 |

Material, Color, and Finish

| | |
|-----------------------------|--|
| Color | Black |
| color rendering index (cri) | 90 |
| color temperature | 2700 ,3000 ,3500 ,4000 ,5000 ,Variable |
| Finish | Matte |
| Lens Color | WHITE |
| Lens Material | Polycarbonate |
| Style | CONTEMPORARY |

Dimensions and Weight

| | |
|--------|-----|
| Height | 1.1 |
| Length | 4.7 |
| Width | 4.7 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Construction | Canless,New Construction,Remodel |
| Description | 4" 9W LED WAFER 27K/3K/35K/4K/5K BLACK 90CRI |
| extra long description | LITH WF4 SWW5 90CRI MB M6 4IN wafer |
| Features | Contractor Select |
| Long Description | The Wafer™ LED Downlights with Switchable White technology provides high-quality light output and efficiency and features a switch for easy color temperature adjustment while eliminating the need for recessed housings. |
| Product Type | Downlight |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | JUNO |
| GTIN | 00194994243595 |
| Manufacturers Part Number | WF4 SWW5 90CRI MB M6 |
| UPC | 194994243595 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type | Downlight |

Trade Size

| | |
|---------------|------|
| aperture size | 4 in |
|---------------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 6 |
| Weight | 1 |
| Weight Per each | 1.15 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Decorative,Hospitality,Residential,Retail,Shower |
| environmental conditions | Indoor,Outdoor |
| Mounting | Recessed |
| standard | CSAusCA Title 24,ENERGY STAR,FCC 47CFR Part 15 Consumer,JA8 |