



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF4SWW590CRIMBM6 4" 9W Led Wafer 27K/3K/35K/4K/5K Black 90cri *Lithonia Lighting - Acuity*

Catalog Number	WF4SWW590CRIMBM6
Manufacturer	Lithonia Lighting - Acuity
Description	The Wafer™ Led Downlights With Switchable White Technology Provides High-Quality Light Output and Efficiency and Features A Switch For Easy Color Temperature Adjustment While Eliminating The Need For Recessed Housings.
Weight per unit	1.2 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimensions	4.7 x 1.1 x 1.1
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	670 LM
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Round
Voltage Rating	120
Warranty	3
Wattage	9

Material, Color, and Finish

Color	Black
color rendering index (cri)	90
color temperature	2700 ,3000 ,3500 ,4000 ,5000 ,Variable
Finish	Matte
Lens Color	WHITE
Lens Material	Polycarbonate
Style	CONTEMPORARY

Dimensions and Weight

Height	1.1
Length	4.7
Width	4.7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	Canless,New Construction,Remodel
Description	4" 9W LED WAFER 27K/3K/35K/4K/5K BLACK 90CRI
extra long description	LITH WF4 SWW5 90CRI MB M6 4IN wafer
Features	Contractor Select
Long Description	The Wafer™ LED Downlights with Switchable White technology provides high-quality light output and efficiency and features a switch for easy color temperature adjustment while eliminating the need for recessed housings.
Product Type	Downlight

Manufacturer Information

Brand	JUNO
GTIN	00194994243595
Manufacturers Part Number	WF4 SWW5 90CRI MB M6
UPC	194994243595

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Downlight

Trade Size

aperture size	4 in
---------------	------

Packaging

Carton	1
Package	6
Weight	1
Weight Per each	1.15

Uses, Certifications, and Standards

Application	Decorative,Hospitality,Residential,Retail,Shower
environmental conditions	Indoor,Outdoor
Mounting	Recessed
standard	CSAusCA Title 24,ENERGY STAR,FCC 47CFR Part 15 Consumer,JA8