



## PRE-CONFIGURED HDMI 2-PORT STRAP, WHITE

WP1011-WH | [On-Q](#)

### FEATURES & BENEFITS

Get the latest in HD with this pre-configured HDMI strap.



Includes two blank ports for use with any keystone insert.  
In-wall HDMI connection.

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Connection Type: HDMI A  
Type: Preconfigured Decorator Strap

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: CAN/CSA-C22.2 No. 182.4-1990  
CSA Standard: Yes  
UL Listing No: ANSI/UL 1863  
UL Standard: Yes  
UN SPSC: 39121704

#### DIMENSIONS

Depth (Metric): 3.2 cm  
Depth (US): 1.25"  
Height (Metric): 10.6 cm  
Height (US): 4.19"  
Width (Metric): 4.2 cm  
Width (US): 1.65"

## TECHNICAL INFORMATION

Jack Connectors: Copper Alloy, Gold over Nickel Plated 19 pin HDMI A Female

Material: High Impact Flame Retardant Plastic

Mounting: Wall Box

OhmValue: 2 ohms max

Receptacle Type: 19 Pin HDMI A Female

Number Of Receptacles: 1x HDMI, 2x Keystone Cutouts



## PRE-CONFIGURED HDMI 2-PORT STRAP, WHITE

WP1011-WH | [On-Q](#)

### FEATURES & BENEFITS

Get the latest in HD with this pre-configured HDMI strap.



Includes two blank ports for use with any keystone insert.  
In-wall HDMI connection.

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Connection Type: HDMI A  
Type: Preconfigured Decorator Strap

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: CAN/CSA-C22.2 No. 182.4-1990  
CSA Standard: Yes  
UL Listing No: ANSI/UL 1863  
UL Standard: Yes  
UN SPSC: 39121704

#### DIMENSIONS

Depth (Metric): 3.2 cm  
Depth (US): 1.25"  
Height (Metric): 10.6 cm  
Height (US): 4.19"  
Width (Metric): 4.2 cm  
Width (US): 1.65"

## TECHNICAL INFORMATION

Jack Connectors: Copper Alloy, Gold over Nickel Plated 19 pin HDMI A Female

Material: High Impact Flame Retardant Plastic

Mounting: Wall Box

OhmValue: 2 ohms max

Receptacle Type: 19 Pin HDMI A Female

Number Of Receptacles: 1x HDMI, 2x Keystone Cutouts