



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WW732GN 3/4"X66' GRN Prem Vny Tape *Nsi Industries*

Catalog Number	WW732GN
Manufacturer	Nsi Industries
Description	Warriorwrap WW-732-GN Green Vinyl Professional-Quality Electrical Tape Is Strong Enough For Demanding Environments and Highly Resistant to Abrasion and Corrosion. This Tape Is 7MIL Thick, 66FT Long and Has A Max Temperature Rating Of 220 Degrees F. The Strong Adhesion Helps Stick to Uneven Surfaces and Keeps The Backing In Place. Top Breaking Strength and Elasticity Make Warriorwrap An Excellent Choice For Splicing, Insulating or Marking Wires.
Weight per unit	0.2200 (lbs/each)
Product Category	Markers & Marking Tapes

### Features

adhesion strength	33.2
Material	Vinyl
maximum voltage	600
Temperature Range	0° - 221°
Tensile Strength	19.8
Warranty	1 YEAR

### Material, Color, and Finish

Backing Material	Plasticized Polyvinyl Chloride (PVC)
Color	Green

### Dimensions and Weight

Length	66
Size	Thickness - 7mil - Length-66' - Width 3/4"
Thickness	.007
Width	.750



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	3/4"X66' GRN PREM VNY TAPE
extra long description	NSI WW-732-GN Vyl Elec Tape Premium
Features	Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. For insulating, splicing or marking cables and wires on the jobsite, choose WarriorWrap, available in 12 colors and 3 grades of quality. That quality starts with strong adhesion to stick to uneven surfaces. But that's not all—it also features the best breaking strength around and unmatched elasticity to hold tight in residential or commercial en
Long Description	WarriorWrap WW-732-GN Green Vinyl Professional-Quality Electrical Tape is strong enough for demanding environments and highly resistant to abrasion and corrosion. This tape is 7mil thick, 66ft long and has a max temperature rating of 220 degrees F. The strong adhesion helps stick to uneven surfaces and keeps the backing in place. Top breaking strength and elasticity make WarriorWrap an excellent choice for splicing, insulating or marking wires.
Product Type	Vyl Elec Tape Premium 7MIL .75" 60FT GR
Special Features	Superior Adhesion and Elasticity, Extreme Weather Performance, Excellent Tensile Strength, Highly Resistant to UV, Abrasion and Corrosion.

## Manufacturer Information

Brand	NSi
GTIN	00662381367211
Manufacturers Part Number	WW-732-GN
UPC	662381367211

## Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Premium

## Packaging

Carton	1
Weight Per each	0.22

## Uses, Certifications, and Standards

Application	NSI
standard	UL 510