



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WW832 3/4"X66' 8.5MIL Prem Vny Tape

Nsi Industries

Catalog Number	WW832
Manufacturer	Nsi Industries
Description	Warriorwrap WW-832 Black Vinyl Heavy Duty Electrical Tape Is Strong Enough For Professional Environments and Highly Resistant to Abrasion and Corrosion. This Tape Is 8.5MIL Thick, 66FT Long and Has A Max Temperature Rating Of 220 Degrees F. The Strong Adhesion Helps Stick to Uneven Surfaces. Top Breaking Strength and Elasticity Make Warriorwrap An Excellent Choice For Splicing, Insulating or Marking Wires.
Weight per unit	0.2500 (lbs/each)
Product Category	Markers & Marking Tapes

Features

Material	Vinyl
maximum voltage	600
Warranty	1 YEAR

Material, Color, and Finish

Backing Material	NSI
Color	Black

Dimensions and Weight

Length	66
Size	Thickness - 8.5mil - Length-66' - Width 3/4"
Thickness	.0085
Width	.750



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	3/4"X66' 8.5MIL PREM VNY TAPE
extra long description	NSI WW-832 Vyl Elec Tape Premium 8.
Features	Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. For insulating, splicing or marking cables and wires on the jobsite, choose WarriorWrap, available in 12 colors and 3 grades of quality. That quality starts with strong adhesion to stick to uneven surfaces. But that's not all—it also features the best breaking strength around and unmatched elasticity to hold tight in residential or commercial en
Long Description	WarriorWrap WW-832 Black Vinyl Heavy Duty Electrical Tape is strong enough for professional environments and highly resistant to abrasion and corrosion. This tape is 8.5mil thick, 66ft long and has a max temperature rating of 220 degrees F. The strong adhesion helps stick to uneven surfaces. Top breaking strength and elasticity make WarriorWrap an excellent choice for splicing, insulating or marking wires.
Product Type	Vyl Elec Tape Premium 8.5MIL .75" 66FT
Special Features	Superior Adhesion and Elasticity, Extreme Weather Performance, Excellent Tensile Strength, Highly Resistant to UV, Abrasion and Corrosion.

Manufacturer Information

Brand	NSi
GTIN	00662381367150
Manufacturers Part Number	WW-832
UPC	662381367150

Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Premium

Packaging

Carton	1
Weight Per each	0.25

Uses, Certifications, and Standards

Application	Primary Insulation for Wire and Cale Splices up to 600 Volts, Wire Harnessing, Used for Jacketing on High Voltage Splices.
standard	UL 510