



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WRD9 1-14AWG AI H Tap

*Nsi Industries*

Catalog Number	WRD9
Manufacturer	Nsi Industries
Description	Dual Rated Wide Range Tap Connectors 6-2 Awg Dual Rated Wide Range Tap Connectors Are Used For Combinations Of Aluminum and Aluminum-Cooper Conductors. Standard Compression Tools and Dies Install In All Sizes. They Have Formable Ribs to Provide Broader Contact Area. Fold-In Tabs Provide Positive Tab Interlock As Tool Closes. Made From High Strength Aluminum Alloy. All Connectors Are Reversible. Rated 600 Volts.
Weight per unit	2.0 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

Conductor Size	1 AWG - 14 AWG
Material	Aluminum
Tap Size	8 AWG - 14 AWG
Voltage Rating	600V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Aluminum
Finish	Aluminum



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	1-14AWG AL H TAP
extra long description	NSI WRD9 Al Wide Range Connector #1
Features	Dual Rated Wide Range Tap Connectors 6-2 AWG Dual rated wide range tap connectors are used for combinations of aluminum and aluminum-cooper conductors. Standard compression tools and dies install in all sizes. They have formable ribs to provide broader contact area. Fold-in tabs provide positive tab interlock as tool closes. Made from high strength aluminum alloy. All connectors are reversible. Rated 600 Volts.
Long Description	Dual Rated Wide Range Tap Connectors 6-2 AWG Dual rated wide range tap connectors are used for combinations of aluminum and aluminum-cooper conductors. Standard compression tools and dies install in all sizes. They have formable ribs to provide broader contact area. Fold-in tabs provide positive tab interlock as tool closes. Made from high strength aluminum alloy. All connectors are reversible. Rated 600 Volts.
Product Type	Al Wide Range Connector #1-8 Awg
Special Features	A Groove-3 4 6 6 (ACSR) - 2 3 4 (STR) - 1 2 3 4 (SOL) - B Groove- 8 10 12 14 (STR) - 8 10 12 14 (SOL)

## Manufacturer Information

Brand	NSi
GTIN	00662381003249
Manufacturers Part Number	WRD9
UPC	662381003249

## Taxonomies, Classifications, and Categories

Category Description	T&B C TAP LUGS
Type	Wide Range Tap Connectors

## Packaging

Carton	1
Weight Per each	2

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
-------------	-----------------------------------------