



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WWHR75 High Volt Rubberless Tape 30 FTX .75 In

Nsi Industries

| | |
|------------------|---|
| Catalog Number | WWHR75 |
| Manufacturer | Nsi Industries |
| Description | Warriorwrap WW-HR-75 Black High-Voltage Linerless Rubber Splicing Tape Is Strong Enough For Professional Environments and Gets The Job Done Right The First Time, Every Time. This Tape Is 30MIL Thick, .75 Inches Wide, 30FT Long and Has An Ethylene Rubber-Based Design. The Self-Bonding Adhesive Helps Stick to Uneven Surfaces and Easily Conforms to Irregular Shapes. Top Breaking Strength and Elasticity Make Warriorwrap An Excellent Choice For Insulating, Jacketing Of Splices On Power Cables, Jacketing Termina |
| Weight per unit | 0.1930 (lbs/each) |
| Product Category | Markers & Marking Tapes - Tape |

Features

| | |
|-------------------|--------------|
| maximum voltage | 69 |
| Temperature Range | 130 C, 266 F |
| Tensile Strength | 333.6 |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|------------------|-----|
| Backing Material | NSI |
|------------------|-----|

Dimensions and Weight

| | |
|-----------|--------------------|
| Length | 30 |
| Thickness | 30 |
| Width | 0.7500000000000000 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | HIGH VOLT RUBBERLESS TAPE 30 FTX .75 IN |
| extra long description | NSI WW-HR-75 Linerless Rubber Tape |
| Features | Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. That quality starts with strong adhesion to stick to uneven surfaces. But that's not all—it also features the best breaking strength around and unmatched elasticity. This high-voltage linerless rubber splicing tape can handle the toughest jobs, like the insulation and jacketing of splices on power cables from 600-Volt up to 69,000 Volt. The self |
| Long Description | WarriorWrap WW-HR-75 Black High-Voltage Linerless Rubber Splicing Tape is strong enough for professional environments and gets the job done right the first time, every time. This tape is 30mil thick, .75 inches wide, 30ft long and has an ethylene rubber-based design. The self-bonding adhesive helps stick to uneven surfaces and easily conforms to irregular shapes. Top breaking strength and elasticity make WarriorWrap an excellent choice for insulating, jacketing of splices on power cables, jacketing termina |
| Product Type | Linerless Rubber Tape HV .75" 30FT |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381365583 |
| Manufacturers Part Number | WW-HR-75 |
| UPC | 662381365583 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------|
| Category Description | TAPE |
|----------------------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 0.193 |