ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



WT31 WIRETWIST WIRE CONNECTOR, WT3 ORANGE, 100/BOX

IDEAL

Catalog Number	WT31
Manufacturer	IDEAL
Description	Wire Twist Connector, (2) #18 AWG Conductor Size, (2) #14 AWG Conductor Size, Orange Insulation Color, +221 °F Operating Temperature, 3 to 5 Conductors, 600 V ac
Weight per unit	0.2600 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

Material, Color, and Finish

Color	Orange

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Descriptions

Description	WIRETWIST WIRE CONNECTOR, WT3 ORANGE, 100/BOX
Features	With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance.The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing
Long Description	Buchanan, Wire Connector, WireTwist, Conductor Range: 22 - 14 AWG, 2/18 AWG Min, 2/14 AWG MAX, Number Of Conductors: 3 to 5, Material: Flame-retardant Polypropelene, Color: Orange, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT3
Product Type	Wire-Twist Conn., Orange, Box100
Special Features	1,000V Maximum In Fixtures And Signs;Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Features: Five Color-Coded Models Cover Common Construction Wire Ranges;Fixed, Square-Wire Spring Threads Itself Creating A Secure Pressure Grip;Model Number: WT3;Ribbed Cap Provides Positive Grip For Fast, Easy Installation;Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F);UL 486C Listed And CSA 22.2 #188 Certified
Extra Long Description	IDEAL WT3-1 WIRE-TWIST CONN.,ORANGE

Manufacturer Information

Brand	Buchanan
	Ideal Industries
GTIN	00781789610047
UPC	783250

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS

Availability

Minimum Qty	100

Packaging

Carton	100
Package	1000
Weight Per Each	0.2600 (lbs/each)

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
Environmental Conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
Standard	CSA C22.2 #188, UL 486C Listed, RoHS