ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



# WT3B Wiretwist Wire Connector, WT3 Orange, 500/Bag

*Ideal*

| | |
|---|---|
| Catalog Number | WT3B |
| Manufacturer | Ideal |
| Description | Buchanan, Wire Connector, Wiretwist, Conductor Range: 22 - 14 Awg, 2/18 Awg Min, 2/14 Awg Max, Number Of Conductors: 3 to 5, Material: Flame-Retardant Polypropelene, Color: Orange, Voltage Rating: 600 V, Environmental Conditions: Tough, Ul 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT3 |
| Weight per unit | 1.1 (lbs/each) |
| Product Category | Electrical Fixture Conn ( Nuts |

## Features

| | |
|---|---|
| Material | Flame-retardant Polypropelene |
| Voltage Rating | 600 |

## Material, Color, and Finish

| | |
|---|---|
| Color | Orange |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Descriptions

| | |
|---|---|
| Description | WIRETWIST WIRE CONNECTOR, WT3 ORANGE, 500/BAG |
| extra long description | IDEAL WT3-B WIRE-TWIST CONN.,ORANGE |
| Features | With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance.The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing |
| Long Description | Buchanan, Wire Connector, WireTwist, Conductor Range: 22 - 14 AWG, 2/18 AWG Min, 2/14 AWG MAX, Number Of Conductors: 3 to 5, Material: Flame-retardant Polypropelene, Color: Orange, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT3 |
| Product Type | Wire-Twist Conn., Orange, Bag500 |
| Special Features | 1,000V Maximum In Fixtures And Signs;Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Features: Five Color-Coded Models Cover Common Construction Wire Ranges;Fixed, Square-Wire Spring Threads Itself Creating A Secure Pressure Grip;Model Number: WT3;Ribbed Cap Provides Positive Grip For Fast, Easy Installation;Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F);UL 486C Listed And CSA 22.2 #188 Certified |

## Manufacturer Information

| | |
|---|---|
| Brand | Buchanan |
| GTIN | 00781789610054 |
| Manufacturers Part Number | WT3-B |
| UPC | 781789610054 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | WIRE NUTS |

## Availability

| | |
|---|---|
| minimum qty | 500 |

## Packaging

| | |
|---|---|
| Carton | 500 |
| Package | 10000 |
| Weight Per each | 1.1 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Insulating or Joining 1 or more conductors |
| environmental conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F) |
| standard | CSA C22.2 #188, UL 486C Listed, RoHS |