



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

206 Stanton St.  
71446-0000, LA Leesville  
Phone: 337-238-1624  
Fax: 337-239-2527



## WWCBC Blu Winged Wire Conn

*Nsi Industries*

Catalog Number	WWCBC
Manufacturer	Nsi Industries
Description	The Easy-Twist WWC-B-C 100-Count Bag Of Blue Winged Wire Connectors Are Designed For Use On Copper Wires In The 14-6 Awg Size Range. Theyâ€™re Made Of Flame-Retardant Thermoplastic Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Swept-Back Wing Design and Ribbed Texture Makes Them Easy to Twist. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You
Weight per unit	0.9000 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Thermoplastic
Number of Conductors	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Type	CU Wire Only

### Material, Color, and Finish

Color	Blue
Finish	Thermoplastic
Housing Material	Thermoplastic

### Dimensions and Weight

Depth	.472
Height	1.57
Size	H=1.57 - W=1.26 - ID=.472



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

206 Stanton St.  
71446-0000, LA Leesville  
Phone: 337-238-1624  
Fax: 337-239-2527

## Descriptions

Description	BLU WINGED WIRE CONN
extra long description	NSI WWC-B-C Winged Blue Easy Twist,
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. The expert team at NSI designed these connectors with key convenience and performance features for electrical in
Long Description	The Easy-Twist WWC-B-C 100-Count Bag of Blue Winged Wire Connectors are designed for use on copper wires in the 14-6 AWG size range. They are made of flame-retardant thermoplastic rated for a maximum temperature of 105°C (221°F Fahrenheit). The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic swept-back wing design and ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or anywhere else you
Product Type	Winged Blue Easy Twist, 14-6 Awg - Carton Of 50
Special Features	Winged Blue Wire Connector - 50 Pcs Carton

## Manufacturer Information

Brand	Easy-Twist
GTIN	00662381361608
Manufacturers Part Number	WWC-B-C
UPC	662381361608

## Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Winged Wire Connectors

## Availability

minimum qty	50
-------------	----

## Packaging

Carton	50
Weight Per each	0.9

## Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C