

ELLIOTT ELECTRIC SUPPLY 2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



Size

WWCGRD GRN Winged Wire Conn Nsi Industries

I	
Catalog Number	WWCGRD
Manufacturer	Nsi Industries
Description	The Easy-Twist WWC-GR-D 25, 000-Count Bulk Fibre Drum Of Green Winged Wire Connectors Are Designed For Grounding Copper Wires In The 14-12 Awg Size Range. They Have A Hole In The Top Designed For A Through-Wire and Are Made Of Flame-Retardant Thermoplastic. The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Swept-Back Wing Design and Ribbed Texture Makes Them Easy to Twist. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere E
Weight per unit	157.5 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts
Features	
Material	Thermoplastic
Number of Conductors	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Type	CU Wire Only
Material, Color, and Finish	
Color	Green
Finish	Thermoplastic
Housing Material	Thermoplastic
Dimensions and Weight	
Depth	327
Height	1.13

H=1.13 - W=.795 - ID=.327



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Descriptions	
Description	GRN WINGED WIRE CONN
extra long description	NSI WWC-GR-D Easy-Twist Winged Tan
Features	Connecting wires is faster and easier than ever with the
	professional performance features of Easy-Twist wire connectors
	from NSI. These connectors feature a specialized design to install
	in half the time of a typical wire connector, saving you time and energy. The GR line includes a hole in the top of the connector
	for a through wire, for use in grounding applications. The conical
	screw shape grips in fewer twists and the outside of the
	connector is textured with easy-grip ribs for comfortable
	twisting. T
Long Description	The Easy-Twist WWC-GR-D 25,000-Count Bulk Fibre Drum of
	Green Winged Wire Connectors are designed for grounding
	copper wires in the 14-12 AWG size range. They have a hole in
	the top designed for a through-wire and are made of
	flame-retardant thermoplastic. The quick-grip square spring
	design grips in fewer twists and can dead-end a single wire, while the ergonomic swept-back wing design and ribbed texture makes
	the ergonomic swept-back wing design and ribbed texture makes them easy to twist. Their compact design is useful for
	applications in tight areas or anywhere e
Product Type	Easy-Twist Winged Tan - STD Jar
Special Features	Winged Green Wire Connector - 25,000 Pcs Drum
Manufacturer Information	9.500.500.500.500.500.500.500.500.500.50
Brand	NSi
GTIN	00662381141620
Manufacturers Part Number	WWC-GR-D
UPC	662381141620
Taxonomies, Classifications, and Ca	ategories
	WIRE NUTS
Туре	Winged Wire Connectors
Availability	
minimum qty	25000
Packaging	
Carton	1
Package	25000
Weight Per each	157.5
Uses, Certifications, and Standards	
Application	Grounding Wire
environmental conditions	105 C
standard	UL 467
4.666.66	