



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WWCGRSJ GRN WNGD Wire Conn 100PC Jar *Nsi Industries*

Catalog Number	WWCGRSJ
Manufacturer	Nsi Industries
Description	The Easy-Twist WWC-GR-SJ 100-Count Small Jar Of Green Winged Wire Connectors Are Designed For Grounding Copper Wires In The 14-12 Awg Size Range. They Have A Hole In The Top Designed For A Through-Wire and Are Made Of Flame-Retardant Thermoplastic. The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Swept-Back Wing Design and Ribbed Texture Makes Them Easy to Twist. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You
Weight per unit	0.7900 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Thermoplastic
Number of Conductors	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Type	CU Wire Only

Material, Color, and Finish

Color	Green
Finish	Thermoplastic

Dimensions and Weight

Depth	.327
Height	1.13
Size	H=1.13 - W=.795 - ID=.327



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	GRN WNGD WIRE CONN 100PC JAR
extra long description	NSI WWC-GR-SJ Easy-Twist Winged Yel
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The GR line includes a hole in the top of the connector for a through wire, for use in grounding applications. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. T
Long Description	The Easy-Twist WWC-GR-SJ 100-Count Small Jar of Green Winged Wire Connectors are designed for grounding copper wires in the 14-12 AWG size range. They have a hole in the top designed for a through-wire and are made of flame-retardant thermoplastic. The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic swept-back wing design and ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or anywhere else you
Product Type	Easy-Twist Winged Yellow - 500 Bag
Special Features	UL 486C

Manufacturer Information

Brand	NSi
GTIN	00662381142504
Manufacturers Part Number	WWC-GR-SJ
UPC	662381142504

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Winged Wire Connectors

Packaging

Carton	1
Package	100
Weight Per jar	0.79

Uses, Certifications, and Standards

Application	Grounding Wire
environmental conditions	105 C
standard	UL 467
Temperature Rating	105 C