

Specifications

Eaton XBUT25D22

Eaton XB IEC terminal block, Screw Connection Multi-Conductor Terminal Blocks, Gray, 12 AWG/2.5 mm² maximum wire, Four-wire

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT25D22
UPC	782116905157
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.2 in
PRODUCT WEIGHT	0.03 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified



Product specifications

TYPE	IEC-XB Series
AMPERAGE RATING	28A (IEC), 20A (UL)
VOLTAGE RATING	IEC 500V, UL 150V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XBUT25D22
--------------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton XBUT25D22

Eaton XB IEC terminal block, Screw Connection Multi-Conductor Terminal Blocks, Gray, 12 AWG/2.5 mm² maximum wire, Four-wire

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT25D22
UPC	782116905157
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.2 in
PRODUCT WEIGHT	0.03 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified



Product specifications

TYPE	IEC-XB Series
AMPERAGE RATING	28A (IEC), 20A (UL)
VOLTAGE RATING	IEC 500V, UL 150V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XBUT25D22
--------------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

