

Eaton XBUT25BK

Catalog Number: XBUT25BK

Eaton XB IEC terminal block, Screw connection single level-through-feed, Black, 12 AWG/2.5 mm² maximum wire



General specifications

| | |
|-----------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton XB IEC terminal block | XBUT25BK |
| UPC | Product Length/Depth |
| 786685231303 | 1.85 in |
| Product Height | Product Width |
| 2.17 in | 0.2 in |
| Product Weight | Warranty |
| 0.02 lb | 1 year |
| Certifications | |
| UL Listed | |
| CSA Certified | |

Type

IEC-XB Series

Amperage Rating

32A (IEC), 22A (EN), 28A (EN), 20A (UL)

Voltage rating

IEC 800V, EN 700V, UL 600V

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT25BK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XBUT25BK

Catalog Number: XBUT25BK

Eaton XB IEC terminal block, Screw connection single level-through-feed, Black, 12 AWG/2.5 mm² maximum wire



General specifications

| | |
|-----------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton XB IEC terminal block | XBUT25BK |
| UPC | Product Length/Depth |
| 786685231303 | 1.85 in |
| Product Height | Product Width |
| 2.17 in | 0.2 in |
| Product Weight | Warranty |
| 0.02 lb | 1 year |
| Certifications | |
| UL Listed | |
| CSA Certified | |

Type

IEC-XB Series

Amperage Rating

32A (IEC), 22A (EN), 28A (EN), 20A (UL)

Voltage rating

IEC 800V, EN 700V, UL 600V

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT25BK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)