

# XCE and XJF Mounting Pans and Hinges

## MOUNTING PANS

Catalog Number (Steel)	Catalog Number (Aluminum)	Catalog Number (Phenolic)	Pan Dimensions Nominal		Enclosure Size Reference Inside width x length	Weight Each (pounds) (Steel)
			Width	Length		
XSM 0416	XSA 0416	XSB 0416	3 1/4	15 1/4	4 x 16	1 1/2
XSM 0608	XSA 0608	XSB 0608	5 1/8	7 1/8	6 x 8	1
XSM 0611	XSA 0611	XSB 0611	5 1/8	10 1/8	6 x 11	1 1/2
XSM 0612	XSA 0612	XSB 0612	5 1/8	11 1/8	6 x 12	1 3/4
XSM 0613	XSA 0613	XSB 0613	5 1/8	12 1/8	6 x 13	2
XSM 0710	XSA 0710	XSB 0710	6 1/8	9 1/8	7 x 10	1 1/4
XSM 0718	XSA 0718	XSB 0718	6 1/8	17 3/8	7 x 18	2 1/2
XSM 0808	XSA 0808	XSB 0808	7	7	8 x 8	1 1/4
XSM 0810	XSA 0810	XSB 0810	7	9 1/8	8 x 10	1 1/2
XSM 0812	XSA 0812	XSB 0812	6 7/8	10 7/8	8 x 12	2 1/4
XSM 0911	XSA 0911	XSB 0911	8	10	9 x 11	2 1/2
XSM 1010	XSA 1010	XSB 1010	8 7/8	8 7/8	10 x 10	2 1/2
XSM 1012	XSA 1012	XSB 1012	10 7/8	8 7/8	10 x 12	3
XSM 1014	XSA 1014	XSB 1014	8 7/8	12 7/8	10 x 14	3 1/2
XSM 1212	XSA 1212	XSB 1212	10 7/8	10 7/8	12 x 12	3 3/4
XSM 1218	XSA 1218	XSB 1218	10 1/2	16 1/2	12 x 18	5 1/2
XSM 1220	XSA 1220	XSB 1220	11	19	12 x 20	6 1/2
XSM 1224	XSA 1224	XSB 1224	11	23	12 x 24	8
XSM 1230	XSA 1230	XSB 1230	10 3/4	28 3/4	12 x 30	9 3/4
XSM 1236	XSA 1236	XSB 1236	10 3/4	34 3/4	12 x 36	11 3/4
XSM 1246	XSA 1246	XSB 1246	10 3/4	44 3/4	12 x 46	15
XSM 1414	XSA 1414	XSB 1414	12 7/8	12 7/8	14 x 14	5
XSM 1422	XSA 1422	XSB 1422	12 7/8	20 7/8	14 x 22	8
XSM 1428	XSA 1428	XSB 1428	12 7/8	26 7/8	14 x 28	10 3/4
XSM 1616	XSA 1616	XSB 1616	14 3/4	14 3/4	16 x 16	6 3/4
XSM 1624	XSA 1624	XSB 1624	14 1/2	22 1/2	16 x 24	10 1/4
XSM 1628	XSA 1628	XSB 1628	26 1/2	14 1/2	16 x 28	12
XSM 1630	XSA 1630	XSB 1630	14 1/2	28 1/2	16 x 30	12 1/2
XSM 1634	XSA 1634	XSB 1634	32 1/2	14 1/2	16 x 34	14 3/4
XSM 1646	XSA 1646	XSB 1646	14 1/2	44 1/2	16 x 46	20 1/4
XSM 1818	XSA 1818	XSB 1818	16 3/4	16 3/4	18 x 18	8 3/4
XSM 1824	XSA 1824	XSB 1824	16 1/2	22 1/2	18 x 24	11 1/2
XSM 1830	XSA 1830	XSB 1830	16 1/2	28 1/2	18 x 30	14 3/4
XSM 1836	XSA 1836	XSB 1836	16 1/2	34 1/2	18 x 36	18
XSM 2036	XSA 2036	XSB 2036	34 1/2	18 1/2	20 x 36	20
XSM 2048	XSA 2048	XSB 2048	46 1/2	18 1/2	20 x 48	27
XSM 2424	XSA 2424	XSB 2424	22	22	24 x 24	15 1/4
XSM 2430	XSA 2430	XSB 2430	22	28	24 x 30	19 1/4
XSM 2436	XSA 2436	XSB 2436	34	22	24 x 36	23 1/2
XSM 3236	XSA 3236	XSB 3236	29	33	32 x 36	28 3/4

### Mounting Pans

#### MATERIAL — Steel: (XSM)

Galvanized 12 gauge steel plate. The catalog number includes the steel mounting pan complete with 1/4" high spacers and stainless steel mounting screws.

**MATERIAL — Aluminum: (XSA)** Consult factory for availability.

#### MATERIAL — Phenolic: (XSB)

A special phenolic laminated material that has high mechanical and dielectric strength. It is excellent for mounting and wiring control equipment. The catalog number includes the phenolic board, 3/8" thick, complete with 1/4" high spacers and stainless steel mounting screws.

**Note:** No installation charge when customer specifies factory installation of mounting pan.

## HINGES

Hinges Catalog Number	Enclosure Size Reference Inside width x length
XHB-2	4 x 16
XHB-2	6 x 8
XHB-2	6 x 11
XHB-2	6 x 12
XHB-2	6 x 13
XHB-2	7 x 10
XHB-2	7 x 18
XHB-2	8 x 8
XHB-2	8 x 10
XHB-2	8 x 12
XHB-2	9 x 11
XHB-2	10 x 10
XHB-2	10 x 12
XHB-2	10 x 14
XHC-2	12 x 12
XHC-2	12 x 18
XHC-2	12 x 20
XHC-2	12 x 24
XHC-2	12 x 30
XHD-3	12 x 36
XHD-4	12 x 46
XHC-2	14 x 14
XHF-2	14 x 22
XHF-2	14 x 28
XHD-2	16 x 16
XHF-2	16 x 24
XHF-2	16 x 28
XHF-2	16 x 30
XHD-3	16 x 34
XHF-4	16 x 46
XHF-2	18 x 18
XHF-2	18 x 24
XHF-2	18 x 30
XHF-3	18 x 36
XHF-3	20 x 36
XHF-4	20 x 48
XHF-2	24 x 24
XHF-2	24 x 30
XHF-3	24 x 36
XHF-3	32 x 36

### Hinge Set

#### Description:

Made of extruded aluminum alloy consisting of two sections, female and male (with stainless steel pin) and four stainless steel hex head bolts. Designed to allow right or left hand removable or non-removable installation.

Unless specified, left hand removable hinge installation will be furnished by factory when hinged enclosures are ordered.

**Note:** Catalog numbers represent complete hinge sets necessary for enclosure assembly.