



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1612 E. Booth Road
72143-0000, AR Searcy
Phone: 501-368-0309
Fax: 501-368-0619



XT0B016BC1 IEC Ovlr Frame B Class 10 10-16a

Eaton Corp

Catalog Number	XT0B016BC1
Manufacturer	Eaton Corp
Description	Overload Relay, Bi-Metallic, Thermal Type; 690 Volt Ac 6 Amp Contact Rating; UL, Csa, Ce Approval; Contactor Mounting; IP20 Enclosure; Screw Terminal Type; 1NO-1NC Auxiliary Contact; 00, 0, 1, 2 Nema Size; 12 to 16 Amp Motor Fla
Weight per unit	0.3000 (lbs/each)
Product Category	Overload Relays & Accessories

Features

Ambient Temperature	COMPENSATED
Auxiliary Contact	1NO-1NC
Contact Rating	690 Volt AC 6 Amp
IEC Size	B
Motor FLA	12 to 16 Amp
Reset Type	Automatic/Manual
Terminal Type	Screw
Trip Class	CLASS 10A

Descriptions

Additional Information	NEMA RoHS/ATEX Compliant; Overall Dimension 1.77 Inch Width x 1.89 Inch Depth x 3.27 Inch Height
Commodity Description	OVERLOAD RELAYS & ACCESSORIES
Description	IEC OVLR FRAME B CLASS 10 10-16A
extra long description	BI-METALLIC, THERMAL TYPE; 690 VOLT AC 6 AMP CONTACT RATING; UL, CSA, CE APPROVAL; IEC CONTACTOR AND STARTER APPLICATION; DIRECT MOUNT MOUNTING; IP20 ENCLOSURE; SCREW TERMINAL TYPE; 1NO-1NC AUXILIARY CONTACT; 12 TO 16 AMP MOTOR FLA; MANUAL/AUTOMATIC RESET TYPE; B IEC SIZE; COMPENSATED AMBIENT TEMPERATURE; CLASS 10A TRIP CLASS; ROHS COMPLIANT; FRAME SIZE 45 MILLIMETER; WIRE SIZE 14 TO 8 AWG; TORQUE RATING 16 INCH-POUND; AMBIENT TEMPERATURE RATING -13 TO 131 DEG F; XTOB MODEL
Long Description	OVERLOAD RELAY, BI-METALLIC, THERMAL TYPE; 690 VOLT AC 6 AMP CONTACT RATING; UL, CSA, CE APPROVAL; CONTACTOR MOUNTING; IP20 ENCLOSURE; SCREW TERMINAL TYPE; 1NO-1NC AUXILIARY CONTACT; 00, 0, 1, 2 NEMA SIZE; 12 TO 16 AMP MOTOR FLA
Product Type	Overload Relay



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1612 E. Booth Road
72143-0000, AR Searcy
Phone: 501-368-0309
Fax: 501-368-0619

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	04015082901684
Manufacturers Part Number	XTOB016BC1
Model	XTOB
UPC	015082901688

Taxonomies, Classifications, and Categories

Category Description	IEC/FREEDOM CONTACTOR
Type	Bi-Metallic, Thermal

Packaging

Carton	1
Weight Per each	0.3

Uses, Certifications, and Standards

Approval	UL, CSA, CE
Enclosure	IP20
Mounting	CONTACTOR
NEMA Size	00, 0, 1, 2